




PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT3I	.06 (1.5)	3.00 (76)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	11.4 (290)	40 (178)	INTERMEDIATE	CURVED	.32 (145)
PLT4I	.06 (1.5)	4.00 (102)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	14.5 (368)	40 (178)	INTERMEDIATE	CURVED	.40 (181)
PLT1S	.06 (1.5)	1.00 (25)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	4.8 (122)	50 (222)	STANDARD	CURVED	.13 (58)
PLT1.5S	.06 (1.5)	1.50 (38)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	6.2 (157)	50 (222)	STANDARD	CURVED	.26 (118)
PLT2S	.06 (1.5)	1.88 (47.8)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	7.4 (188)	50 (222)	STANDARD	CURVED	.29 (132)
PLT2.5S	.06 (1.5)	2.50 (63.5)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	9.8 (249)	50 (222)	STANDARD	CURVED	.38 (173)
PLT3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	11.5 (292)	50 (222)	STANDARD	CURVED	.45 (204)

NOTES:

*1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, & PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

						TITLE						
						PAN-TY CABLE TIES - PLT SERIES						
						CUSTOMER DRAWING						
						ITEM REVISION NAME						
						W10001CB/31						
						DATASET FILE NAME		MATERIAL: NYLON 6.6				
						W10001CB/31 SS-5540 SH2						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x : - - - .xxx ± .020 [.51] .xx ± .02 [.5] ANGLES : - - -						
						THIRD ANGLE PROJECTION						
31	8/13/13	BWG	KJM	RTFI	CORRECTED REV NO. REMOVED NOTE 1. SEE ECN FOR DETAILS.	SS-5540/30	DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER:	SIZE
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	CEW	12-27-84	HVP	NONE	SHT 1 OF 1	A