

AC / DC ADAPTORS

MULTIPLE CHOICE SELECTION - 300mA

OUTPUT: 1.5, 3, 4.5, 6, 7.5, 9, 12VDC @ 300mA

Here's a device that conserves batteries conveniently and reliably on most equipment. Adaptor plugs into ordinary 120VAC 60Hz house current. Choose any of the above voltages. Has built-in polarity reversal switch. Employs a full wave bridge rectifier, with 1000mfd filter capacitor for good regulation and lowest hum level. Six interchangeable plugs are included with the unit to serve most power-up needs. The plugs are: 2.5mm, 3.5mm, 2.1mm x 5.5mm, 2.5mm x 5.5mm, 1.35mm x 3.5mm, 1.7mm x 4.0mm & 9 volt snap adaptor. **UL Listed.**



No. BE226

EXTRA HEAVY DUTY MULTIPLE CHOICE SELECTION - 800mA

OUTPUT SELECTION:

OFF, 3, 4.5, 6, 7.5, 9, 12VDC @ 800mA

Six interchangeable plugs are included with the unit to serve most power-up needs. The plugs are: 2.5mm, 3.5mm, 2.1mm x 5.5mm, 2.5mm x 5.5mm, 1.35mm x 3.5mm, 1.7mm x 4.0mm & 9 volt snap adaptor.

- Plug-in Polarity Reversal
- Plugs into 120VAC / 60Hz house current
- 6-1/2 foot cord
- Circuit employs full range bridge rectifier with filter capacitor for excellent regulation and elimination of AC "hum".



No. BE240

Universal Regulated Switching Power Supply 1000mA Switchable Power Supply

This Hi-Tech product is ideal for all Electronic consumer products which require DC voltages of 3, 4.5, 6, 7.5, 9, or 12V DC and current up to 1000mA. Use with such products as CD players, Radios, Cassette Recorders, Electronic games, mini TV, Palm Computer and many other battery appliances.

Specifications:

Inputs: 100-140V AC @60Hz
Output: 3, 4.5, 6.0, 7.5, 12V DC
Current: 0-1000mA

Plug sizes: 3.5mm, 2.35 x 0.75mm, 3.0 x 1.0mm, 3.5 x 1.35mm, 4.0 x 1.7mm, 5.0 x 2.5mm, 2.5mm, 5.5 x 2.1mm, 5.5 x 2.5mm, (O.D. x I.D.)

Features

- Constant Voltage
- Independent of load
- Short Circuit Protection
- Automatic Thermal Cut Off
- Automatic Overload Cut Off
- Folding AC Plug for Travel
- 6 Different Adaptor Plugs
- Concealed Voltage selector
- UL/CUL Listed

No. 48-1088 Multi-voltage Power Supply



DIGITAL CAMERA POWER SUPPLY

Casio, Epson, Fuji, Kodak, Minolta, Ricoh, Toshiba, Viviter, Hewlett Packard, Olympus, Nikon, Konica, AGFA,

This innovative Hi-Tech product is ideal for most **Digital Cameras** which require a 3.0, 3.3, 5.0, 6.0, 6.5, or 7V supply and any current up to 2100mA. It comes with 4 different individual adaptor plugs.

No. 48-1190 Digital Camera Power Supply

Features:

- Constant Voltage
- Independent of load
- Short Circuit Protection
- Automatic Thermal Cut Off
- Automatic Overload Cut Off
- UL/CUL Listed

Specifications:

Inputs: 100-140V AC @60Hz
Output: 3, 3.3, 5.0, 6.0, 6.5, 7V DC
Current: 0-2100mA

Plug sizes: 4.0 x 1.7mm, 4.75 x 1.75mm, 3.5 x 1.35mm, 2.35 x 0.75mm (O.D. x I.D.)



WORLD TRAVELER AC/DC ADAPTOR (600mA)



Plug sizes: 5.5 x 2.5mm, 5.5 x 2.1mm, 5.5 x 1.5mm, 5.0 x 2.1mm, 3.5 x 1.35mm, 3.5mm. (O.D. x I.D.)

This model is designed for travelers. Dual voltage 110/220V with two flat pin and additional two round pin adaptor plug. Enables the traveler to use this adaptor in parts of most continents e.g. North and South America, Asia, Middle East and Europe. 1.5, 3, 4.5, 6, 7.5, 9, 12VDC with LED indicator and six most common detachable single plugs. Fits most all appliances e.g. radios, cassette recorders, handheld games, calculators, portable phones, toys, office equipment and other electronic products.

No. 48-140

MINI BATTERY TESTER

No. BC148

Check power on all types of batteries - D, C, AA, AAA, 9 volt, N and Button Cells.

Fits in pocket or purse. Requires no outside power source. Great gift, promo item, or give away.

