


Sockets

BO 10



Product	BO 10	
description	Bright metal 4 mm diameter nickel-plated brass socket, with M6 thread. For installation in equipment chassis and switch panels from 1.5 mm till 8.0 mm wall thickness.	
operating instruction	BA403	
Articlenummer	930160000 Ni	
drawing		
		
technical data		
connection	M6 thread	
rated voltage ⁽¹⁾	30 VAC / 60 VDC	
measurement cat. acc. to IEC 61010	O ⁽³⁾	
rated current ⁽¹⁾ (consider derating curve)	16 A	
material socket	brass, nickel plated	
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to +100 °C	
standard	IEC 61010	

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

⁽³⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 12.09.2018