




AMP WIRE RANGE	FILE E13288
16-14 AWG STRANDED	16-14 AWG STRANDED

SECTION B-B

SECTION A-A

-	-	2.92-4.83 [.115-.190]	1 2-165075-0
-	-	2.92-4.32 [.115-.170]	2 165075-1
1000	LOOSE PIECE	2.92-4.83 [.115-.190]	165075
QTY	PACKAGE TYPE	FOR WIRE INSULATION "A"	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 04JUN07	TE TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK T MICHELUTTI 04JUN07		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHELUTTI 04JUN07	NAME	
0 PLC ± -		PRODUCT SPEC	TERMINAL, WIRE PIN, PLASTI-GRIP,	
1 PLC ± 0.5[.02]		APPLICATION SPEC		
2 PLC ± 0.20[.007]		WEIGHT	SIZE A2	CAGE CODE 00779
3 PLC ± -		CUSTOMER DRAWING	DRAWING NO C=165075	RESTRICTED TO -
4 PLC ± -		SCALE 8:1	SHEET 1 of 1	REV K2
ANGLES ± 1°				
FINISH				
MATERIAL				