



- | | | | | | | | | |
|----|----------|----------------|-----------------|---|---|------------------------------|---------------|---|
| 11 | OBSOLETE | 0.43
[.017] | 11.94
[.470] |  |  | 0.64 X 0.64
[.025 X .025] | 2 | 4-205361-9 |
| | OBSOLETE | 0.43
[.017] | 16.74
[.659] |  |  | 0.64 X 0.64
[.025 X .025] | 3 | 4-205361-8 |
| 11 | OBSOLETE | 0.43
[.017] | 6.63
[.261] |  |  | 0.64 X 0.64
[.025 X .025] | 1 | 3-205361-3 |
| | OBSOLETE | 0.43
[.017] | 11.94
[.470] |  |  | 0.64 X 0.64
[.025 X .025] | 2 |  4-205361-6 |
| | OBSOLETE | - | 20.57
[.810] |  |  | 0.79 X 1.57
[.031 X .062] | 3 | 1-205361-3 |
| | OBSOLETE | 0.25
[.010] | 16.74
[.659] |  |  | 0.56 X 0.91
[.022 X .036] | 3 | 1-205361-0 |
| | OBSOLETE | 0.13
[.005] | 20.57
[.810] |  |  | 1.14 X 1.14
[.045 X .045] | 3 | 205361-6 |
| | OBSOLETE | 0.43
[.017] | 16.74
[.659] |  |  | 0.64 X 0.64
[.025 X .025] | 3 | 205361-3 |
| | OBSOLETE | 0.43
[.017] | 16.74
[.659] |  |  | 0.64 X 0.64
[.025 X .025] | 3 | 205361-2 |
| | | 0.43
[.017] | 16.74
[.659] |  |  | 0.64 X 0.64
[.025 X .025] | 3 | 205361-1 |
| | | B | A | FINISH
CONTACT
POST | FINISH
CONTACT
BODY | CONTACT
POST | NO OF
TERM | PART
NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT						DWG NO.	07/07/92				Tyco Electronics Corporation	
						CHECKED BY	J. STONE				Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROVED BY		NAME	PIN ASSY, 34 POSITION POSTED, M SERIES —					
		0 PL/C	± —	PRODUCT SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO						
		2 PL/C	± —	APPLICATION SPEC								
		M PL/C	± 0.13 [.005]									
MATERIAL		ANGLES	± —	WEIGHT		A1 00779 © 205361 —						
HOUSING: 1		FINISH	SEE TABLE	CUSTOMER DRAWING		SCALE		2:1		SHEET	1 OF 1	REV U