



Ovalgrip Straight Cut

Features and Benefits

Ovalgrip markers have been specifically designed to mark cable and wire both before and after termination.

Their oval shape means that these markers are easy to fit by hand directly onto the cable pre termination or they can be attached as an identification flag post termination using special marker Arrowtags. Arrowtags fitted with Ovalgrip are fastened using cable ties and can very easily be modified or removed without the need to uninstall the cable.

Sizes 50 and 85 can be used with Arrowtags for identifying larger cable bundles.



A simple idea for complex marking needs.

Application

Ideally suited to panel building, mass transit, utilities, telecommunications and electrical contracting.

These markers are supplied continuous on a reel (HODS).


Markers are available as a standard in yellow material marked in black and international resistor colour code. Characters are 0-9, A-Z and standard electrical symbols.

White material marked in black available on special request.

AT1 Arrowtags will fit 7 size 50 markers.

AT2 Arrowtags will fit 8 size 85 markers.

AT3 Arrowtags will fit 14 size 85 markers.



Ovalgrip straight cut.

Material Data	
Material	Flexible Polyvinyl Chloride, cadmium free (PVC)
Colour	White, yellow, international resistor colour code
Operating Temperature	-65 °C to +105 °C, Intermittent +135 °C
Flammability	Self extinguishing
Specification	BS 2782-540B, BS 6746C, UL224, IEC 304, IEC 757



For details on Arrowtags please see page 345.



Technical Table

Type	Quantity per kit	Outside Ø min.	Outside Ø max.	Length (L)	Recommended Carrier
HODS50*	1000	1.7	3.60	4.0	AT1
HODS85*	1000	1.8	6.30	4.5	AT2/AT3

All dimensions in mm. Subject to technical changes.

* Marking text 0-9 as international resistor code, as well as A-Z, 0-9 and special characters in yellow.



HODS50 colour code

Article-No.	Type
	531-15365 HODS50
	531-15366 HODS50
	531-15367 HODS50
	531-15368 HODS50
	531-15314 HODS50
	531-15370 HODS50
	531-15371 HODS50
	531-15372 HODS50
	531-15373 HODS50
	531-15374 HODS50

HODS85 colour code

Article-No.	Type
	531-07728 HODS85
	531-07729 HODS85
	531-07730 HODS85
	531-07731 HODS85
	531-07732 HODS85
	531-07733 HODS85
	531-07734 HODS85
	531-07735 HODS85
	531-07736 HODS85
	531-07737 HODS85

HODS50 yellow

Article-No.	Type
	531-15014 HODS50
	531-15024 HODS50
	531-15034 HODS50
	531-15044 HODS50
	531-15054 HODS50
	531-15064 HODS50
	531-15074 HODS50
	531-15084 HODS50
	531-15094 HODS50
	531-15104 HODS50
	531-15114 HODS50
	531-15124 HODS50
	531-15134 HODS50
	531-15144 HODS50
	531-15154 HODS50
	531-15164 HODS50
	531-15174 HODS50
	531-15184 HODS50
	531-15194 HODS50
	531-15204 HODS50
	531-15214 HODS50
	531-15224 HODS50
	531-15234 HODS50
	531-15244 HODS50
	531-15254 HODS50
	531-15264 HODS50
	531-00451 HODS50
	531-00452 HODS50
	531-00175 HODS50
	531-00176 HODS50
	531-00174 HODS50
	531-15274 HODS50
	531-15284 HODS50
	531-15294 HODS50
	531-15304 HODS50
	531-15314 HODS50
	531-15324 HODS50
	531-15334 HODS50
	531-15344 HODS50
	531-15354 HODS50
	531-15364 HODS50

HODS85 yellow

Article-No.	Type
	531-07935 HODS85
	531-07936 HODS85
	531-07937 HODS85
	531-07938 HODS85
	531-07939 HODS85
	531-07940 HODS85
	531-07941 HODS85
	531-07942 HODS85
	531-07943 HODS85
	531-07944 HODS85
	531-07945 HODS85
	531-07946 HODS85
	531-07947 HODS85
	531-07948 HODS85
	531-07949 HODS85
	531-07950 HODS85
	531-07951 HODS85
	531-07952 HODS85
	531-07953 HODS85
	531-07954 HODS85
	531-07955 HODS85
	531-07956 HODS85
	531-07957 HODS85
	531-07958 HODS85
	531-07959 HODS85
	531-07960 HODS85
	531-07924 HODS85
	531-07923 HODS85
	531-07961 HODS85
	531-00386 HODS85
	531-00384 HODS85
	531-07925 HODS85
	531-07926 HODS85
	531-07927 HODS85
	531-07928 HODS85
	531-07732 HODS85
	531-07930 HODS85
	531-07931 HODS85
	531-07932 HODS85
	531-07933 HODS85
	531-07934 HODS85