






## DIMENSIONS: mm (in.)



PCB Layout

**Electrical Specifications:**

- Rating: 50mA/12VDC
- Life: 500,000 cycles
- Contact resistance: 100mΩ max.
- Insulation resistance: 100MΩ min. @ 500VDC
- Dielectric Strength: 250VAC for 1 minute

**Mechanical Specifications:**

- Type: SPST
- Operating force: 160±50g
- Operating temperature: -25°~+70°C
- Storage temperature: -30°~+80°C
- Travel: .012±.004" (.30±.10mm)

**Materials:**

- Cover: tin plated steel
- Contacts: silver clad phosphor bronze
- Terminals: silver clad brass
- Base: nylon, brown
- Stem: nylon, brown

**Note:**

- RoHS Compliant and are also process compatible with 260° solder

**Tactile Switch (SMT)**  
101-0624-EV

**Mountain**  
**Switch**

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0624-EV](#)