

PRODUCT SPECIFICATION

CKI: Carl Kammerling
International Ltd.

Brand	Kasp
Product Range	Premium brass padlocks
Catalogue number	125
Date	15/01/2008

Range Description Premium brass padlocks	
Features • Hardened steel shackle (20mm and above) – extra protection against hacksaw and cropping attacks • Double bolted locking mechanism (30mm and above) – extra strength to resist torsion and pull attacks • Solid brass body – added resistance to corrosion • Anti pick mushroom pins (30mm and above) – extra protection against picking • Paracentric keyway (20mm and above) extra protection against manipulation Derivatives • Stainless steel shackle – maximum resistance against corrosion • Long shackle – provides greater shackle clearance for versatility • Brass shackle – Anti spark and added resistance to corrosion • Closed shackle – additional protection from shackle attack	 K125 series  Long shackle  Closed shackle

Item Number	Item Description	EAN No	Commodity code	Carton Qty
K12515D	Premium brass padlock 15mm - display packed	5013969900262	83011000	6
K12515A1	Premium brass padlock 15mm KA25151 – boxed	5013969900255	83011000	12
K12515D2	Premium brass padlock 15mm twin pack – display packed	5013969900279	83011000	6
K12520	Premium brass padlock 20mm – boxed	5013969900286	83011000	12
K12520D	Premium brass padlock 20mm – display packed	5013969900316	83011000	6
K12520D2	Premium brass padlock 20mm twin pack – display packed	5013969900323	83011000	6
K12520D4	Premium brass padlock 20mm quad pack – display packed	5013969900330	83011000	6
K12520A1	Premium brass padlock 20mm KA25201 – boxed	5013969900293	83011000	12
K12520A2	Premium brass padlock 20mm KA25202 – boxed	5013969900309	83011000	12
K12525	Premium brass padlock 25mm – boxed	5013969900347	83011000	12
K12525D	Premium brass padlock 25mm – display packed	5013969900378	83011000	6
K12525D2	Premium brass padlock 25mm twin pack – display packed	5013969900385	83011000	6
K12525A1	Premium brass padlock 25mm KA25251 – boxed	5013969900354	83011000	12
K12525A2	Premium brass padlock 25mm KA25252 – boxed	5013969900361	83011000	12
K12530	Premium brass padlock 30mm – boxed	5013969900392	83011000	12
K12530D	Premium brass padlock 30mm – display packed	5013969900439	83011000	6
K12530D2	Premium brass padlock 30mm twin pack – display packed	5013969900446	83011000	6
K12530A1	Premium brass padlock 30mm KA25301 – boxed	5013969900408	83011000	12
K12530A2	Premium brass padlock 30mm KA25302 – boxed	5013969900415	83011000	12
K12530A3	Premium brass padlock 30mm KA25303 – boxed	5013969900422	83011000	12
K12530L70BD	Premium brass padlock 30mm with 70mm brass long shackle – display packed	5013969900453	83011000	6
K12535D	Premium brass padlock 35mm – display packed	5013969900477	83011000	6
K12540	Premium brass padlock 40mm – boxed	5013969900484	83011000	12
K12540D	Premium brass padlock 40mm – display packed	5013969900590	83011000	6
K12540D2	Premium brass padlock 40mm twin pack – display packed	5013969900606	83011000	6
K12540D4	Premium brass padlock 40mm quad pack – display packed	5013969900613	83011000	6
K12540A1	Premium brass padlock 40mm KA25401 – boxed	5013969900491	83011000	12
K12540A2	Premium brass padlock 40mm KA25402 – boxed	5013969900507	83011000	12
K12540A3	Premium brass padlock 40mm KA25403 – boxed	5013969900514	83011000	12
K12540A4	Premium brass padlock 40mm KA25404 – boxed	5013969900521	83011000	12
K12540L40	Premium brass padlock 40mm with 40mm long shackle – boxed	5013969900620	83011000	6
K12540L40D	Premium brass padlock 40mm with 40mm long shackle – boxed	5013969900644	83011000	6
K12540L40A1	Premium brass padlock 40mm with 40mm long shackle KA – boxed	5013969900637	83011000	6
K12540KA	Premium brass padlock 40mm KA – boxed	5013969902167	83011000	6
K12540L63	Premium brass padlock 40mm with 63mm long shackle – boxed	5013969900651	83011000	6
K12540L63D	Premium brass padlock 40mm with 63mm long shackle – display packed	5013969900682	83011000	6

K12540L63A1	Premium brass padlock 40mm with 63mm long shackle KA – boxed	5013969900682	83011000	6
K12540L63BD	Premium brass padlock 40mm with 63mm brass long shackle – display packed	5013969900675	83011000	6
K12540SA	Premium brass padlock 40mm semi assembled – boxed	5013969901474	83011000	6
K12540SD	Premium brass padlock 40mm with stainless steel shackle – display packed	5013969900699	83011000	6
K12540XD	Premium brass padlock 40mm closed shackle – display packed	5013969900705	83011000	6
K12545D	Premium brass padlock 45mm – display packed	5013969900712	83011000	6
K12550	Premium brass padlock 50mm – boxed	5013969900729	83011000	6
K12550D	Premium brass padlock 50mm – display packed	5013969900774	83011000	6
K12550D2	Premium brass padlock 50mm twin pack – display packed	5013969900781	83011000	4
K12550A1	Premium brass padlock 50mm KA25501 – boxed	5013969900736	83011000	6
K12550A2	Premium brass padlock 50mm KA25502 – boxed	5013969900743	83011000	6
K12550A3	Premium brass padlock 50mm KA25503 – boxed	5013969900750	83011000	6
K12550A4	Premium brass padlock 50mm KA25504 – boxed	5013969900767	83011000	6
K12550KA	Premium brass padlock 50mm KA – boxed	5013969902174	83011000	6
K12550L80	Premium brass padlock 50mm with 80mm long shackle – boxed	5013969900798	83011000	6
K12550L80D	Premium brass padlock 50mm with 80mm long shackle – display packed	5013969900811	83011000	6
K12550L80A1	Premium brass padlock 50mm with 80mm long shackle KA – boxed	5013969900804	83011000	6
K12550SD	Premium brass padlock 50mm with stainless steel shackle – display packed	5013969900828	83011000	6
K12550XD	Premium brass padlock 50mm closed shackle – display packed	5013969900835	83011000	6
K12560	Premium brass padlock 60mm – boxed	5013969900842	83011000	6
K12560D	Premium brass padlock 60mm – display packed	5013969900873	83011000	6
K12560A1	Premium brass padlock 60mm KA25601 – boxed	5013969900859	83011000	6
K12560A2	Premium brass padlock 60mm KA25602 – boxed	5013969900866	83011000	6
K12560KA	Premium brass padlock 60mm KA25603 – boxed	5013969902181	83011000	6
K12560SA	Premium brass padlock 60mm semi assembled – boxed	5013969901498	83011000	6
K12540DTL	Premium Brass toolbox lock 40mm – display packed	5013969900590	83011000	6
K12540DCLIP	Premium Brass Toolbox lock Clip Strip 6 x K12540DTL	5013969902778	83011000	1
K12515A2	Premium brass padlock 15mm KA25152 – boxed	5013969901511	83011000	12
K12520A3	Premium brass padlock 20mm KA25203 – boxed	5013969901528	83011000	12
K12520A4	Premium brass padlock 20mm KA25204 – boxed	5013969901535	83011000	12
K12525A3	Premium brass padlock 25mm KA25253 – boxed	5013969901542	83011000	12
K12525A4	Premium brass padlock 25mm KA25254 – boxed	5013969901559	83011000	12
K12530A4	Premium brass padlock 30mm KA25304 – boxed	5013969901566	83011000	12
K12530A5	Premium brass padlock 30mm KA25305 – boxed	5013969901573	83011000	12
K12530A6	Premium brass padlock 30mm KA25306 – boxed	5013969901580	83011000	12
K12540A5	Premium brass padlock 40mm KA25405 – boxed	5013969901597	83011000	12
K12540A6	Premium brass padlock 40mm KA25406 – boxed	5013969901603	83011000	12

K12540A7	Premium brass padlock 40mm KA25407 – boxed	5013969901610	83011000	12
K12550A5	Premium brass padlock 50mm KA25505 – boxed	5013969901627	83011000	6
K12550A6	Premium brass padlock 50mm KA25506 – boxed	5013969901634	83011000	6
K12550A7	Premium brass padlock 50mm KA25507 – boxed	5013969901641	83011000	6
K12560A3	Premium brass padlock 60mm KA25603 – boxed	5013969901658	83011000	6
K12560A4	Premium brass padlock 60mm KA25604 – boxed	5013969901665	83011000	6
K12540L40A5	Premium brass padlock 40mm with 40mm long shackle KA25405 – boxed	5013969901672	83011000	12
K12540L63A5	Premium brass padlock 40mm with 63mm long shackle KA25505 – boxed	5013969901689	83011000	12
K12550L80A5	Premium brass padlock 40mm with 63mm long shackle KA25505 – boxed	5013969901696	83011000	6
K12540MK	Premium brass padlock 40mm master keyed – boxed		83011000	1
K12550MK	Premium brass padlock 50mm master keyed – boxed		83011000	1
K12560MK	Premium brass padlock 60mm master keyed – boxed		83011000	1
K12550SA	Premium brass padlock 50mm semi assembled – boxed	5013969901481	83011000	6

Technical product information	Body – Solid brass																																																					
	Locking mechanism- Pin tumbler cylinder type																																																					
	Security rating, key differs and Use environment:																																																					
	<table> <tr> <th>Item</th><th>Security rating</th><th>Key differs</th><th>Pins</th><th>Use Environment</th></tr> <tr> <td>K12515</td><td>1</td><td>8</td><td>3</td><td>Light outdoor use</td></tr> <tr> <td>K12520</td><td>2</td><td>34</td><td>3</td><td>Light outdoor use</td></tr> <tr> <td>K12525</td><td>3</td><td>202</td><td>4</td><td>Light outdoor use</td></tr> <tr> <td>K12530</td><td>4</td><td>420</td><td>4</td><td>Light outdoor use</td></tr> <tr> <td>K12535</td><td>4</td><td>420</td><td>4</td><td>Light outdoor use</td></tr> <tr> <td>K12540</td><td>5</td><td>1988</td><td>5</td><td>Light outdoor use</td></tr> <tr> <td>K12545</td><td>6</td><td>1988</td><td>5</td><td>Light outdoor use</td></tr> <tr> <td>K12550</td><td>7</td><td>1988</td><td>5</td><td>Light outdoor use</td></tr> <tr> <td>K12560</td><td>10</td><td>1988</td><td>5</td><td>Light outdoor use</td></tr> </table>					Item	Security rating	Key differs	Pins	Use Environment	K12515	1	8	3	Light outdoor use	K12520	2	34	3	Light outdoor use	K12525	3	202	4	Light outdoor use	K12530	4	420	4	Light outdoor use	K12535	4	420	4	Light outdoor use	K12540	5	1988	5	Light outdoor use	K12545	6	1988	5	Light outdoor use	K12550	7	1988	5	Light outdoor use	K12560	10	1988	5
Item	Security rating	Key differs	Pins	Use Environment																																																		
K12515	1	8	3	Light outdoor use																																																		
K12520	2	34	3	Light outdoor use																																																		
K12525	3	202	4	Light outdoor use																																																		
K12530	4	420	4	Light outdoor use																																																		
K12535	4	420	4	Light outdoor use																																																		
K12540	5	1988	5	Light outdoor use																																																		
K12545	6	1988	5	Light outdoor use																																																		
K12550	7	1988	5	Light outdoor use																																																		
K12560	10	1988	5	Light outdoor use																																																		
The above applies to all derivatives of the basic body size																																																						
Shackle Dimensions and materials:																																																						
<table> <tr> <th>Dimensions mm</th><th>Dia</th><th>Internal width</th><th>Internal height</th><th>Material</th></tr> <tr> <td>K12515D</td><td>2.8</td><td>8</td><td>12</td><td>Brass</td></tr> <tr> <td>K12520</td><td>3.5</td><td>9</td><td>12</td><td>Hardened steel</td></tr> </table>					Dimensions mm	Dia	Internal width	Internal height	Material	K12515D	2.8	8	12	Brass	K12520	3.5	9	12	Hardened steel																																			
Dimensions mm	Dia	Internal width	Internal height	Material																																																		
K12515D	2.8	8	12	Brass																																																		
K12520	3.5	9	12	Hardened steel																																																		

	K12525	4	13	13	Hardened steel
	K12530	4.8	16	17	Hardened steel
	K12535D	5.5	19	19	Hardened steel
	K12540	6.4	22	22	Hardened steel
	K12540L40	6.4	22	40	Hardened steel
	K12540L63	6.4	22	63	Hardened steel
	K12540XD	6.4	14	18	Hardened steel
	K12545D	7.1	25	25	Hardened steel
	K12550	8	27	29	Hardened steel
	K12550L80	8	27	80	Hardened steel
	K12550XD	8	19	20	Hardened steel
	K12560	9.5	34	34	Hardened steel
	Recommended applications- Luggage, cupboards, lockers, toolboxes, sheds etc.				
Standards compliance	None applicable				
User health and safety information	None applicable				
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations				
Material safety data	None applicable				
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered				
Country of origin	China				

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K12515D	16	10	33	24	140	12	170	55
K12515A1	16	10	33	24	18	17	36	25
K12515D2	16	10	33	24	140	12	170	76
K12520	20	10	35	35	24	17	41	36
K12520D	20	10	35	35	140	12	170	66
K12520D2	20	10	35	35	140	12	170	97
K12520D4	20	10	35	35	155	13	170	159
K12520A1	20	10	35	35	25	18	45	37
K12520A2	20	10	35	35	25	18	45	37
K12525	25	12	43	58	28	18	48	59
K12525D	25	12	43	58	140	17	170	88
K12525D2	25	12	43	58	140	17	170	147
K12525A1	25	12	43	58	28	18	48	59
K12525A2	25	12	43	58	28	18	48	59
K12530	30	13	50	89	35	21	56	93
K12530D	30	13	50	89	140	20	170	121
K12530D2	30	13	50	89	140	24	170	204
K12530A1	30	13	50	89	35	21	56	93
K12530A2	30	13	50	89	35	21	56	93
K12530A3	30	13	50	89	35	21	56	93
K12530L70BD	30	13	104	102	140	16	190	140
K12535D	35	13	55	116	140	22	170	147
K12540	40	15	63	155	43	20	70	161
K12540D	40	15	63	155	140	20	170	184
K12540D2	40	15	63	155	156	20	170	337
K12540D4	40	15	63	155	210	20	170	640
K12540A1	40	15	63	155	43	20	70	161
K12540A2	40	15	63	155	43	20	70	161
K12540A3	40	15	63	155	43	20	70	161
K12540A4	40	15	63	155	43	20	70	161
K12540L40	40	15	80	164	45	17	80	170
K12540L40D	40	15	80	164	140	20	170	193

K12540L40A1	40	15	80	164	45	17	80	170
K12540KA	40	15	80	164	45	17	80	170
K12540L63	40	15	103	175	45	17	105	182
K12540L63D	40	15	103	175	140	21	170	206
K12540L63A1	40	15	103	175	45	17	105	182
K12540L63BD	40	15	103	175	140	21	170	206
K12540SA	40	15	63	155	43	20	70	161
K12540SD	40	15	63	155	43	20	70	161
K12540XD	40	15	61	192	140	25	170	222
K12545D	45	15	68	194	140	18	170	225
K12550	50	17	77	277	52	20	78	284
K12550D	50	17	77	277	140	18	170	305
K12550D2	50	17	77	277	155	23	170	577
K12550A1	50	17	77	277	52	20	78	284
K12550A2	50	17	77	277	52	20	78	284
K12550A3	50	17	77	277	52	20	78	284
K12550A4	50	17	77	277	52	20	78	284
K12550KA	50	17	77	277	52	20	78	284
K12550L80	50	17	127	315	52	20	130	325
K12550L80D	50	17	127	315	140	20	220	352
K12550L80A1	50	17	127	315	52	20	130	325
K12550SD	50	17	77	277	140	18	170	305
K12550XD	50	17	75	336	140	23	170	365
K12560	60	19	90	422	65	20	90	432
K12560D	60	19	90	422	150	25	190	455
K12560A1	60	19	90	422	65	20	90	432
K12560A2	60	19	90	422	65	20	90	432
K12560KA	60	19	90	422	65	20	90	432
K12560SA	60	19	90	422	65	20	90	432
K12540DTL	40	15	63	155	140	20	170	184
K12540DCLIP								
K12515A2	16	10	33	24	18	17	36	25
K12520A3	20	10	35	35	25	18	45	37
K12520A4	20	10	35	35	25	18	45	37
K12525A3	25	12	43	58	28	18	48	59
K12525A4	25	12	43	58	28	18	48	59
K12530A4	30	13	50	89	35	21	56	93

K12530A5	30	13	50	89	35	21	56	93
K12530A6	30	13	50	89	35	21	56	93
K12540A5	40	15	63	155	43	20	70	161
K12540A6	40	15	63	155	43	20	70	161
K12540A7	40	15	63	155	43	20	70	161
K12550A5	50	17	77	277	52	20	78	284
K12550A6	50	17	77	277	52	20	78	284
K12550A7	50	17	77	277	52	20	78	284
K12560A3	60	19	90	422	65	20	90	432
K12560A4	60	19	90	422	65	20	90	432
K12540L40A5	40	15	80	164	45	17	80	170
K12540L63A5	40	15	103	175	45	17	105	182
K12550L80A5	50	17	127	315	52	20	130	325
K12540MK	40	15	63	155	43	20	70	161
K12550MK	50	17	77	277	52	20	78	284
K12560MK	60	19	90	422	65	20	90	432
K12550SA	50	17	77	277	52	20	78	284

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K12515D	145	185	68	391		
K12515A1	56	82	36	312		
K12515D2	145	185	65	212		
K12520	57	100	42	449		
K12520D	145	185	68	458		
K12520D2	145	185	68	644		
K12520D4	165	185	68	1021		
K12520A1	57	100	42	449		
K12520A2	57	100	42	449		
K12525	60	120	50	730		
K12525D	145	185	68	591		
K12525D2	145	185	68	945		
K12525A1	60	120	50	730		

K12525A2	60	120	50	730		
K12530	75	135	56	1146		
K12530D	145	180	75	790		
K12530D2	145	195	75	1295		
K12530A1	75	135	56	1146		
K12530A2	75	135	56	1146		
K12530A3	75	135	56	1146		
K12530L70BD	145	280	65	924		
K12535D	145	185	68	946		
K12540	95	130	73	1976		
K12540D	145	195	75	1177		
K12540D2	165	215	70	2102		
K12540D4	195	225	75	3936		
K12540A1	95	130	73	1976		
K12540A2	95	130	73	1976		
K12540A3	95	130	73	1976		
K12540A4	95	130	73	1976		
K12540L40	85	115	45	1009		
K12540L40D	145	220	80	1223		
K12540L40A1	85	115	45	1009		
K12540KA	85	115	45	1009		
K12540L63	107	120	47	1081		
K12540L63D	145	240	75	1314		
K12540L63A1	107	120	47	1081		
K12540L63BD	145	240	75	1314		
K12540SA	95	130	73	1976		
K12540SD	95	130	73	1976		
K12540XD	145	215	80	1395		
K12545D	145	205	75	1425		
K12550	70	113	80	1740		
K12550D	150	215	80	1911		
K12550D2	165	245	45	2373		
K12550A1	70	113	80	1740		
K12550A2	70	113	80	1740		
K12550A3	70	113	80	1740		
K12550A4	70	113	80	1740		
K12550KA	70	113	80	1740		

K12550L80	110	140	65	1995		
K12550L80D	155	230	105	2216		
K12550L80A1	110	140	65	1995		
K12550SD	150	215	80	1911		
K12550XD	150	225	85	2276		
K12560	70	140	90	2637		
K12560D	160	250	90	2820		
K12560A1	70	140	90	2637		
K12560A2	70	140	90	2637		
K12560KA	70	140	90	2637		
K12560SA	70	140	90	2637		
K12540DTL	145	195	75	1177		
K12540DCLIP	130	20	920	1180		
K12515A2	56	82	36	312		
K12520A3	57	100	42	449		
K12520A4	57	100	42	449		
K12525A3	60	120	50	730		
K12525A4	60	120	50	730		
K12530A4	75	135	56	1146		
K12530A5	75	135	56	1146		
K12530A6	75	135	56	1146		
K12540A5	95	130	73	1976		
K12540A6	95	130	73	1976		
K12540A7	95	130	73	1976		
K12550A5	70	113	80	1740		
K12550A6	70	113	80	1740		
K12550A7	70	113	80	1740		
K12560A3	70	140	90	2637		
K12560A4	70	140	90	2637		
K12540L40A5	85	115	45	1009		
K12540L63A5	107	120	47	1081		
K12550L80A5	110	140	65	1995		
K12540MK	95	130	73	1976		
K12550MK	70	113	80	1740		
K12560MK	70	140	90	2637		
K12550SA	70	113	80	1740		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K12515D	24	Blister	7	Backing card			61	Box
K12515A1			1	Box			12	Box
K12515D2	24	Blister	7	Backing card			62	Box
K12520			1	Box			17	Box
K12520D	24	Blister	7	Backing card			62	Box
K12520D2	24	Blister	7	Backing card			62	Box
K12520D4	27	Blister	7	Backing card			67	Box
K12520A1			1	Box			17	Box
K12520A2			1	Box			17	Box
K12525			1	Box			22	Box
K12525D	24	Blister	7	Backing card			63	Box
K12525D2	24	Blister	7	Backing card			63	Box
K12525A1			1	Box			22	Box
K12525A2			1	Box			22	Box
K12530			4	Box			30	Box
K12530D	24	Blister	7	Backing card			65	Box
K12530D2	24	Blister	7	Backing card			71	Box
K12530A1			4	Box			30	Box
K12530A2			4	Box			30	Box
K12530A3			4	Box			30	Box
K12530L70BD	28	Blister	10	Backing card			84	Box
K12535D	24	Blister	7	Backing card			64	Box
K12540			6	Box			44	Box
K12540D	24	Blister	7	Backing card			73	Box
K12540D2	24	Blister	7	Backing card			80	Box
K12540D4	30	Blister	10	Backing card			96	Box
K12540A1			6	Box			44	Box
K12540A2			6	Box			44	Box
K12540A3			6	Box			44	Box
K12540A4			6	Box			44	Box
K12540L40			6	Box			25	Box

K12540L40D	22	Blister	7	Backing card			63	Box
K12540L40A1			7	Box			25	Box
K12540KA			7	Box			25	Box
K12540L63			7	Box			31	Box
K12540L63D	24	Blister	7	Backing card			78	Box
K12540L63A1			7	Box			31	Box
K12540L63BD			7	Box			31	Box
K12540SA			7	Box			31	Box
K12540SD	24	Blister	7	Backing card			73	Box
K12540XD	23	Blister	7	Backing card			65	Box
K12545D	23	Blister	7	Backing card			75	Box
K12550			7	Box			36	Box
K12550D	22	Blister	7	Backing card			81	Box
K12550D2	22	Blister	7	Backing card			90	Box
K12550A1			7	Box			36	Box
K12550A2			7	Box			36	Box
K12550A3			7	Box			36	Box
K12550A4			7	Box			36	Box
K12550KA			7	Box			36	Box
K12550L80			10	Box			45	Box
K12550L80D	27	Blister	10	Backing card			104	Box
K12550L80A1			10	Box			45	Box
K12550SD	22	Blister	7	Backing card			81	Box
K12550XD	22	Blister	7	Backing card			81	Box
K12560			10	Box			45	Box
K12560D	23	Blister	10	Backing card			96	Box
K12560A1			10	Box			45	Box
K12560A2			10	Box			45	Box
K12560KA			10	Box			45	Box
K12560SA			10	Box			45	Box
K12540DTL	24	Blister	7	Backing card			73	Box
K12540DCLIP	144	Blisters	42	Backing cards	76	Bag & clip strip		
K12515A2			1	Box			12	Box
K12520A3			1	Box			17	Box
K12520A4			1	Box			17	Box
K12525A3			1	Box			22	Box
K12525A4			1	Box			22	Box

K12530A4			4	Box			30	Box
K12530A5			4	Box			30	Box
K12530A6			4	Box			30	Box
K12540A5			6	Box			44	Box
K12540A6			6	Box			44	Box
K12540A7			6	Box			44	Box
K12550A5			7	Box			36	Box
K12550A6			7	Box			36	Box
K12550A7			7	Box			36	Box
K12560A3			10	Box			45	Box
K12560A4			10	Box			45	Box
K12540L40A5			7	Box			25	Box
K12540L63A5			7	Box			31	Box
K12550L80A5			10	Box			45	Box
K12540MK			6	Box			44	Box
K12550MK			7	Box			36	Box
K12560MK			10	Box			45	Box
K12550SA			7	Box			36	Box