





JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	*MSCP $\pm 25\%$	*LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
6PSB	6.0	.140	.120	1.51	15,000	C-2F
12PSB	12.0	.170	.478	6.01	12,000	C-2F
24PSB	24.0	.073	.502	6.31	10,000	C-2F
28PSB	28.0	.040	.287	3.61	6,000	C-2F
35PSB	35.0	.040	.300	3.77	5,000	C-2F
48PSB	48.0	.053	.558	7.01	10,000	CC-2F
60PSB	60.0	.050	.717	9.01	7,500	C-13
120PSB	120.0	.025	.359	4.51	5,000	CC-7A

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION				
					TITLE		T-2 TELEPHONE SLIDE BASE ANSI #5-28mol				
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	DRAWN BY	APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.	SLIDE BASE ANSI #5-28mol		
B	ADD LAMP NUMBER 35PSB	5/17/01	L. WENGSTROM	QC	5/17/01	A	55335				
A	CHANGE FILAMENT TYPE ON 60PSB	8/31/00									
	RELEASED	8/16/00									
			- CAD DRAWING -		SCALE		RELEASED DATE		REVISION DATE	REV. NO.	SHEET
			MANUAL REVISIONS NOT PERMITTED		NONE		8/16/00		5/17/01	B	1 OF 1