

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


50-16-0281

Status:

Active

Description:

15.88mm Pitch Phenolic Range Receptacle Housing



Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

Agency Certification

CSA

LR19980

General

Product Family

Crimp Housings

Series

2481

Application

Signal, Wire-to-Board

Product Name

Range Receptacle

UPC

800753874992

Physical

Circuits (maximum)

2

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Net Weight

20.500/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

15.88mm

Stackable

No

Temperature Range - Operating

0°C to +150°C

Material Info

Old Part Number

2481

Reference - Drawing Numbers

Sales Drawing

SD-2481-*

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2481Series

Mates With

2589

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION