




- VDC: 5, 12
- RPM: 2600~5000
- CFM: 7.67~15.12
- Impeller: 7 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 24g




## DC FAN 60x60x11.5mm

### Specification

|           | Bearing                                              | Voltage | Current | Speed | Input Power | Air Flow | Static Pressure       | Noise | Weight |
|-----------|------------------------------------------------------|---------|---------|-------|-------------|----------|-----------------------|-------|--------|
| MODEL NO  | ○ Sleeve<br>● One ball and one sleeve<br>○ Hydraulic | (Vdc)   | (Amp)   | (Rpm) | (Watts)     | (CFM)    | (mm/H <sub>2</sub> O) | dB(A) | Gram   |
| B6010B12L | ●                                                    | 12      | 0.07    | 3300  | 0.84        | 9.44     | 1.59                  | 28.0  | 24     |
| B6010B12M | ●                                                    | 12      | 0.08    | 3900  | 0.96        | 11.18    | 2.28                  | 32.6  | 24     |
| B6010B12H | ●                                                    | 12      | 0.13    | 4500  | 1.56        | 13.11    | 2.77                  | 36.4  | 24     |
| C6010B05M | ●                                                    | 5       | 0.19    | 3900  | 0.95        | 11.18    | 2.28                  | 32.6  | 24     |
| C6010B12E | ●                                                    | 12      | 0.05    | 2600  | 0.60        | 7.67     | 1.06                  | 23.7  | 24     |
| C6010B12L | ●                                                    | 12      | 0.07    | 3300  | 0.84        | 9.44     | 1.59                  | 28.0  | 24     |
| C6010B12M | ●                                                    | 12      | 0.10    | 3900  | 1.20        | 11.18    | 2.28                  | 32.6  | 24     |
| C6010B12H | ●                                                    | 12      | 0.10    | 4500  | 1.20        | 13.11    | 2.77                  | 36.4  | 24     |
| C6010B12U | ●                                                    | 12      | 0.16    | 5000  | 1.92        | 15.12    | 3.55                  | 40.0  | 24     |
| D6010B05M | ●                                                    | 5       | 0.19    | 3900  | 0.95        | 11.18    | 2.28                  | 32.6  | 24     |
| D6010B12L | ●                                                    | 12      | 0.07    | 3300  | 0.84        | 9.44     | 1.59                  | 28.0  | 24     |
| D6010B12M | ●                                                    | 12      | 0.08    | 3900  | 0.96        | 11.18    | 2.28                  | 32.6  | 24     |
| D6010B12H | ●                                                    | 12      | 0.10    | 4500  | 1.20        | 13.11    | 2.77                  | 36.4  | 24     |
| F6010B12E | ●                                                    | 12      | 0.05    | 2600  | 0.60        | 7.67     | 1.06                  | 23.7  | 24     |
| F6010B12L | ●                                                    | 12      | 0.06    | 3300  | 0.72        | 9.44     | 1.59                  | 28.0  | 24     |
| F6010B12M | ●                                                    | 12      | 0.10    | 3900  | 1.20        | 11.18    | 2.28                  | 32.6  | 24     |
| F6010B12H | ●                                                    | 12      | 0.13    | 4500  | 1.56        | 13.11    | 2.77                  | 36.4  | 24     |

Design specifics subject to change without notice.



### STATIC PRESSURE

