

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010112033

Status:

Active

Overview:

KK®

Description:

2.54mm (.100") Pitch KK® Crimp Terminal Housing, High Pressure, 3 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-7879 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Overview

Product Name

Crimp Housings

7880

KK®

KK®

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Material - Resin

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Stackable

Temperature Range - Operating

3

Natural (White)

94V-0

Female

No

Nylon

1

Bag

No

0.100 In

2.54 mm

No

0°C to +75°C

Electrical

CSA

UL

LR19980

E29179

Material Info

Old Part Number

7880-3B


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-7879

SD-7880



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7880Series

Mates With

2.54mm (.100") Pitch KK® Crimp Terminal Housing, High Pressure, 3 Circuits

Use With

7879 KK® High Pressure Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION