


ALL DIMENSION IN MM UNLESS OTHERWISE STATED : 0.= ± 0.1 mm 00.= ± 0.2 mm 000.= ± 0.3 mm

HEAVY POWER CO., LTD.
A Specialist Manufacturer

No.7, Lane 106, Wukung 3rd. Road,
Wuku Industrial Park, Taipei Hsien,
Taiwan 248
Tel : 886-2-22983178
Fax : 886-2-22983183

Scale :

Date : 2012.02.08

TITLE :

PUSH-IN WIRE CONNECTORS

PART NO. PC258-BK

Housing Material : Polyamide 66 (PA66), flame-retardant to UL 94V-2
Clamp unit : Copper plate , tin-plated
Current : 24A(VDE)
Voltage : 600V(cULus), 450V(VDE)
Working Temp : 110°C
Wire Range : 1.0~2.5mm², #12-#22 AWG, Sol Cu
Stripping Length : 11mm (0.43inch)

International Approvals

cULus : E-113650
CE, VDE, FIMKO, KEMA, CEBEC

PREPARED

yao

REV.

1.0

DWG NO.

PC258-BK