

SolderPro™70

The standard manual ignition multi-function for engineers and technicians. 25W-80W equivalent electrical power.



Applications

- Electrical/Electronic Circuit Repair
- Light Plumbing
- Jewelry, Eyeglass Frame Repair
- Model Building
- Arts and Crafts
- Dental Wax Corrections
- Thawing Frozen Locks
- Install Heat Shrink Tubing
- Install Heat Shrinkable Connectors
- Cut foam & plastics
- Caulterize rope ends

Specifications

Equivalent to a power range 25-80 watts. Cordless, simple, safe operation anywhere. Ready to use 20 seconds after ignition. Tank contains fuel for 120 minutes of operation. No cords, can be used anywhere. No electrical interference. Comes with soldering tip and protective cap.

Length w/Cap	220 mm (8.7 in)
Length w/Soldering tip	190 mm (7.5 in)
Length w/blow torch tip	172 mm (6.8 in)
Weight (when gas-filled)	76 g
Approximate temperature soldering tip	210~450°C (410~850°F)
Torch	1300°C (2400°F)
Gas container capacity	20 ml
Operating capacity (one gas filling)	120 min. at mid setting