

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0874390600

Status:

Active - Custom

Overview:

Pico-Spox™

Description:

1.50mm (.059") Pitch Pico-SPOX™ Wire-to-Board Housing, 6 Circuits, Off-White Housing

Documents:

3D Model

Drawing (PDF)

Product Specification PS-87437 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Overview

Product Literature Order No

Product Name

Crimp Housings

87439

Pico-Spox™

USA-235

Pico-SPOX™

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Lock to Mating Part

Material - Resin

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Polarized to Mating Part

Stackable

Temperature Range - Operating

6

Natural

94V-0

Female

No

Yes

Nylon

1

Bag

No

0.059 In

1.50 mm

Yes

No

-55°C to +105°C

Electrical

CSA

Current - Maximum

UL

LR19980

1.5A, 2A, 3A

E29179

Material Info


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-87437, RPS-87437, RPS-87437-001,
RPS-87437-200

SD-87439-**00



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Halogen-Free



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

87439Series

Mates With

Pico-SPOX™ Wire-to-Board Header [87437](#) , [87438](#)

Use With

[87421](#) Pico-SPOX™ Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION