



Flanged Block Forks – Non-Insulated Butted Seam




Product Number†	UPC (054007-)	Wire Range (AWG)	Stud Size	W	C	L	E	Thickness	Barrel Length	Barrel I.D.	Terminals per Case
MU18-6FFBK	01247	22-18	6	0.30	0.25	0.65	0.50	0.030	0.25	0.070	1000
MU18-8FFBK	01248	22-18	8	0.30	0.25	0.65	0.50	0.030	0.25	0.070	1000
MU18-10FFBK	01249	22-18	10	0.30	0.25	0.65	0.50	0.030	0.25	0.070	1000
MU14-6FFBK	01613	16-14	6	0.30	0.25	0.65	0.50	0.030	0.25	0.090	1000
MU14-8FFBK	01614	16-14	8	0.30	0.25	0.65	0.50	0.030	0.25	0.090	1000
MU14-10FFBK	01615	16-14	10	0.30	0.25	0.65	0.50	0.030	0.25	0.090	1000
MU10-6FFBK	02023	12-10	6	0.32	0.29	0.73	0.54	0.040	0.25	0.135	500
MU10-8FFBK	02024	12-10	8	0.32	0.29	0.73	0.54	0.040	0.25	0.135	500
MU10-10FFBK	02925	12-10	10	0.32	0.29	0.73	0.54	0.040	0.25	0.135	500




MU18-6FFB
Stud Size 6
Wire Range 22-18




MU18-8FFB
Stud Size 8
Wire Range 22-18




MU18-10FFB
Stud Size 10
Wire Range 22-18




MU14-6FFB
Stud Size 6
Wire Range 16-14




MU14-8FFB
Stud Size 8
Wire Range 16-14




MU14-10FFB
Stud Size 10
Wire Range 16-14



MU10-6FFB
Stud Size 6
Wire Range 12-10



MU10-8FFB
Stud Size 8
Wire Range 12-10



MU10-10FFB
Stud Size 10
Wire Range 12-10