

## Wall-Mount Enclosures and Accessories

### Continuous Hinge with 3-Point Latch, Type 4X



#### Industry Standards

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997  
cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66

Meets NEMA Type 3RX requirements

#### Application

These enclosures feature Hoffman's exclusive POWERGLIDE® Handle with 3-point latching, ideal for indoor or outdoor applications that require corrosion protection, convenient access, and padlocking security.

#### Standard Product

| Catalog Number   | AxBxC in./mm                             | Stainless Steel Type | F in./mm   | Steel Panel | Conductive Panel | Stainless Steel Panel | Panel Size D x E in./mm     | Data Pocket |
|------------------|------------------------------------------|----------------------|------------|-------------|------------------|-----------------------|-----------------------------|-------------|
| A24H2006SSLP3PT  | 24.00 x 20.00 x 6.00<br>610 x 508 x 152  | 304                  | 3.00<br>76 | A24P20      | A24P20G          | A24P20SS6             | 21.00 x 17.00<br>533 x 432  | Small       |
| A24H2006SS6LP3PT | 24.00 x 20.00 x 6.00<br>610 x 508 x 152  | 316L                 | 3.00<br>76 | A24P20      | A24P20G          | A24P20SS6             | 21.00 x 17.00<br>533 x 432  | Small       |
| A24H2008SSLP3PT  | 24.00 x 20.00 x 8.00<br>610 x 508 x 203  | 304                  | 3.00<br>76 | A24P20      | A24P20G          | A24P20SS6             | 21.00 x 17.00<br>533 x 432  | Small       |
| A24H2008SS6LP3PT | 24.00 x 20.00 x 8.00<br>610 x 508 x 203  | 316L                 | 3.00<br>76 | A24P20      | A24P20G          | A24P20SS6             | 21.00 x 17.00<br>533 x 432  | Small       |
| A24H2408SSLP3PT  | 24.00 x 24.00 x 8.00<br>610 x 610 x 203  | 304                  | 3.00<br>76 | A24P24      | A24P24G          | A24P24SS6             | 21.00 x 21.00<br>533 x 533  | Small       |
| A24H2408SS6LP3PT | 24.00 x 24.00 x 8.00<br>610 x 610 x 203  | 316L                 | 3.00<br>76 | A24P24      | A24P24G          | A24P24SS6             | 21.00 x 21.00<br>533 x 533  | Small       |
| A30H2408SSLP3PT  | 30.00 x 24.00 x 8.00<br>762 x 610 x 203  | 304                  | 3.00<br>76 | A30P24      | A30P24G          | A30P24SS6             | 27.00 x 21.00<br>686 x 533  | Large       |
| A30H2408SS6LP3PT | 30.00 x 24.00 x 8.00<br>762 x 610 x 203  | 316L                 | 3.00<br>76 | A30P24      | A30P24G          | A30P24SS6             | 27.00 x 21.00<br>686 x 533  | Large       |
| A30H3008SSLP3PT  | 30.00 x 30.00 x 8.00<br>762 x 762 x 203  | 304                  | 3.00<br>76 | A30P30      | A30P30G          | A30P30SS6             | 27.00 x 27.00<br>686 x 686  | Large       |
| A30H3008SS6LP3PT | 30.00 x 30.00 x 8.00<br>762 x 762 x 203  | 316L                 | 3.00<br>76 | A30P30      | A30P30G          | A30P30SS6             | 27.00 x 27.00<br>686 x 686  | Large       |
| A36H2408SSLP3PT  | 36.00 x 24.00 x 8.00<br>914 x 610 x 203  | 304                  | 3.00<br>76 | A36P24      | A36P24G          | A36P24SS6             | 33.00 x 21.00<br>838 x 533  | Large       |
| A36H2408SS6LP3PT | 36.00 x 24.00 x 8.00<br>914 x 610 x 203  | 316L                 | 3.00<br>76 | A36P24      | A36P24G          | A36P24SS6             | 33.00 x 21.00<br>838 x 533  | Large       |
| A36H3008SSLP3PT  | 36.00 x 30.00 x 8.00<br>914 x 762 x 203  | 304                  | 3.00<br>76 | A36P30      | A36P30G          | A36P30SS6             | 33.00 x 27.00<br>838 x 686  | Large       |
| A36H3008SS6LP3PT | 36.00 x 30.00 x 8.00<br>914 x 762 x 203  | 316L                 | 3.00<br>76 | A36P30      | A36P30G          | A36P30SS6             | 33.00 x 27.00<br>838 x 686  | Large       |
| A48H3608SSLP3PT  | 48.00 x 36.00 x 8.00<br>1219 x 914 x 203 | 304                  | 3.00<br>76 | A48P36      | A48P36G          | A48P36SS6             | 45.00 x 33.00<br>1143 x 838 | Large       |
| A48H3608SS6LP3PT | 48.00 x 36.00 x 8.00<br>1219 x 914 x 203 | 316L                 | 3.00<br>76 | A48P36      | A48P36G          | A48P36SS6             | 45.00 x 33.00<br>1143 x 838 | Large       |
| A24H2010SSLP3PT  | 24.00 x 20.00 x 10.00<br>610 x 508 x 254 | 304                  | 3.00<br>76 | A24P20      | A24P20G          | A24P20SS6             | 21.00 x 17.00<br>533 x 432  | Small       |

#### Specifications

- 14 gauge Type 304 or 316L stainless steel bodies and doors
- Seams continuously welded and ground smooth
- Seamless foam-in-place gasket
- Rolled lip around three sides of door
- Internal 3-point latch and Type 316L stainless steel padlocking POWERGLIDE Handle
- Remove door by pulling stainless steel continuous hinge pin
- Data pocket is high-impact thermoplastic
- Collar studs provided for mounting optional panels
- Exterior hardware on Type 316L stainless steel enclosures matches enclosure material
- Bonding provision on door; grounding stud on body

#### Finish

Door, sides, top and bottom have smooth #4 brushed finish. Handle is electropolished.

#### Accessories

See also Accessories.

Panels for Type 3R, 4, 4X, 12 and 13 Enclosures

Steel and Stainless Steel Window Kits

H2OMIT® Vent Drains, Type 4X

H2OMIT® Thermoelectric Dehumidifier

#### Modification and Customization

Hoffman excels at modifying and customizing products to your specifications. Contact your local Hoffman sales office or distributor for complete information.

Bulletin: A4SW3

|                  |                                           |                      |            |             |                  |                       | Panel Size                  |             |
|------------------|-------------------------------------------|----------------------|------------|-------------|------------------|-----------------------|-----------------------------|-------------|
| Catalog Number   | AxBxC in./mm                              | Stainless Steel Type | F in./mm   | Steel Panel | Conductive Panel | Stainless Steel Panel | D x E in./mm                | Data Pocket |
| A24H2010SS6LP3PT | 24.00 x 20.00 x 10.00<br>610 x 508 x 254  | 316L                 | 3.00<br>76 | A24P20      | A24P20G          | A24P20SS6             | 21.00 x 17.00<br>533 x 432  | Small       |
| A36H3010SSLP3PT  | 36.00 x 30.00 x 10.00<br>914 x 762 x 254  | 304                  | 3.00<br>76 | A36P30      | A36P30G          | A36P30SS6             | 33.00 x 27.00<br>838 x 686  | Large       |
| A36H3010SS6LP3PT | 36.00 x 30.00 x 10.00<br>914 x 762 x 254  | 316L                 | 3.00<br>76 | A36P30      | A36P30G          | A36P30SS6             | 33.00 x 27.00<br>838 x 686  | Large       |
| A42H3010SSLP3PT  | 42.00 x 30.00 x 10.00<br>1067 x 762 x 254 | 304                  | 3.00<br>76 | A42P30      | A42P30G          | A42P30SS6             | 39.00 x 27.00<br>991 x 686  | Large       |
| A48H3610SSLP3PT  | 48.00 x 36.00 x 10.00<br>1219 x 914 x 254 | 304                  | 3.00<br>76 | A48P36      | A48P36G          | A48P36SS6             | 45.00 x 33.00<br>1143 x 838 | Large       |
| A48H3610SS6LP3PT | 48.00 x 36.00 x 10.00<br>1219 x 914 x 254 | 316L                 | 3.00<br>76 | A48P36      | A48P36G          | A48P36SS6             | 45.00 x 33.00<br>1143 x 838 | Large       |
| A24H2412SSLP3PT  | 24.00 x 24.00 x 12.00<br>610 x 610 x 305  | 304                  | 3.00<br>76 | A24P24      | A24P24G          | A24P24SS6             | 21.00 x 21.00<br>533 x 533  | Small       |
| A24H2412SS6LP3PT | 24.00 x 24.00 x 12.00<br>610 x 610 x 305  | 316L                 | 3.00<br>76 | A24P24      | A24P24G          | A24P24SS6             | 21.00 x 21.00<br>533 x 533  | Small       |
| A30H2412SSLP3PT  | 30.00 x 24.00 x 12.00<br>760 x 610 x 305  | 304                  | 3.00<br>76 | A30P24      | A30P24G          | A30P24SS6             | 27.00 x 21.00<br>686 x 533  | Large       |
| A30H2412SS6LP3PT | 30.00 x 24.00 x 12.00<br>762 x 610 x 305  | 316L                 | 3.00<br>76 | A30P24      | A30P24G          | A30P24SS6             | 27.00 x 21.00<br>686 x 533  | Large       |
| A36H3012SSLP3PT  | 36.00 x 30.00 x 12.00<br>914 x 762 x 305  | 304                  | 3.00<br>76 | A36P30      | A36P30G          | A36P30SS6             | 33.00 X 27.00<br>838 x 686  | Large       |
| A36H3012SS6LP3PT | 36.00 x 30.00 x 12.00<br>914 x 762 x 305  | 316L                 | 3.00<br>76 | A36P30      | A36P30G          | A36P30SS6             | 33.00 X 27.00<br>838 x 686  | Large       |
| A36H3612SSLP3PT  | 36.00 x 36.00 x 12.00<br>914 x 914 x 305  | 304                  | 3.00<br>76 | A36P36      | A36P36G          | A36P36SS6             | 33.00 x 33.00<br>838 x 838  | Large       |
| A36H3612SS6LP3PT | 36.00 x 36.00 x 12.00<br>914 x 914 x 305  | 316L                 | 3.00<br>76 | A36P36      | A36P36G          | A36P36SS6             | 33.00 x 33.00<br>838 x 838  | Large       |
| A42H3612SSLP3PT  | 42.00 x 36.00 x 12.00<br>1067 x 914 x 305 | 304                  | 3.00<br>76 | A42P36      | A42P36G          | A42P36SS6             | 39.00 x 33.00<br>991 x 838  | Large       |
| A48H3612SSLP3PT  | 48.00 x 36.00 x 12.00<br>1219 x 914 x 305 | 304                  | 3.00<br>76 | A48P36      | A48P36G          | A48P36SS6             | 45.00 x 33.00<br>1143 x 838 | Large       |
| A48H3612SS6LP3PT | 48.00 x 36.00 x 12.00<br>1219 x 914 x 305 | 316L                 | 3.00<br>76 | A48P36      | A48P36G          | A48P36SS6             | 45.00 x 33.00<br>1143 x 838 | Large       |
| A60H3612SSLP3PT  | 60.00 x 36.00 x 12.00<br>1524 x 914 x 305 | 304                  | 3.00<br>76 | A60P36      | A60P36G          | A60P36SS6             | 57.00 x 33.00<br>1448 x 838 | Large       |
| A60H3612SS6LP3PT | 60.00 x 36.00 x 12.00<br>1524 x 914 x 305 | 316L                 | 3.00<br>76 | A60P36      | A60P36G          | A60P36SS6             | 57.00 x 33.00<br>1448 x 838 | Large       |
| A48H3616SSLP3PT  | 48.00 x 36.00 x 16.00<br>1219 x 914 x 406 | 304                  | 3.00<br>76 | A48P36      | A48P36G          | A48P36SS6             | 45.00 x 33.00<br>1143 x 838 | Large       |
| A48H3616SS6LP3PT | 48.00 x 36.00 x 16.00<br>1219 x 914 x 406 | 316L                 | 3.00<br>76 | A48P36      | A48P36G          | A48P36SS6             | 45.00 x 33.00<br>1143 x 838 | Large       |
| A60H3616SSLP3PT  | 60.00 x 36.00 x 16.00<br>1524 x 914 x 406 | 304                  | 3.00<br>76 | A60P36      | A60P36G          | A60P36SS6             | 57.00 x 33.00<br>1448 x 838 | Large       |
| A60H3616SS6LP3PT | 60.00 x 36.00 x 16.00<br>1524 x 914 x 406 | 316L                 | 3.00<br>76 | A60P36      | A60P36G          | A60P36SS6             | 57.00 x 33.00<br>1448 x 838 | Large       |

Purchase panels separately. Optional stainless steel, composite and aluminum panels are available for most sizes.

