

Male headers soldering technique

0.635 mm, standard

art. no.	dim. [mm]			art. no.	dim. [mm]				
	A	B	C		A	B	C		
SL 11 112 ...	11.20	3.00	5.40	SL 1 025 ...	11.20	2.60	5.80		
SL 11 124 ...	12.40	3.00	6.60	SL 1 053 ...	13.90	5.80	5.30		
SL 11 139 ...	13.90	3.00	8.10	SL 1 078 ...	16.40	5.80	7.80		
SL 11 164 ...	16.40	3.00	10.60	SL 1 104 ...	19.00	5.80	10.40		
SL 11 190 ...	19.00	3.00	13.20	SL 1 128 ...	21.40	5.80	12.80		
SL 11 214 ...	21.40	3.00	15.60	SL 1 154 ...	24.00	5.80	15.40		
SL 11 240 ...	24.00	3.00	18.20	SL 1 179 ...	26.50	5.80	17.90		
SL 11 265 ...	26.50	3.00	20.70	SL 1 230 ...	31.60	5.80	23.00		
SL 11 316 ...	31.60	3.00	25.80						
art. no.	dim. [mm]			art. no.	dim. [mm]				
	A	B	C		A	B	C		
SL 22 112 ...	11.20	3.00	5.40	SL 2 025 ...	11.20	2.60	5.80		
SL 22 124 ...	12.40	3.00	6.60	SL 2 053 ...	13.90	5.80	5.30		
SL 22 139 ...	13.90	3.00	8.10	SL 2 078 ...	16.40	5.80	7.80		
SL 22 164 ...	16.40	3.00	10.60	SL 2 104 ...	19.00	5.80	10.40		
SL 22 190 ...	19.00	3.00	13.20	SL 2 128 ...	21.40	5.80	12.80		
SL 22 214 ...	21.40	3.00	15.60	SL 2 154 ...	24.00	5.80	15.40		
SL 22 240 ...	24.00	3.00	18.20	SL 2 179 ...	26.50	5.80	17.90		
SL 22 265 ...	26.50	3.00	20.70	SL 2 230 ...	31.60	5.80	23.00		
SL 22 316 ...	31.60	3.00	25.80						
please indicate:									
		... no. of contacts		... surface					
		one row 1-36		S =selective gold-plated					
		two rows 2-72		G=gold-plated					
				Z =tin-plated					

Every pin length is available on request.