


EVEREADY 1222

9V



Industry Standard Dimensions




Specifications




Classification:	Super Heavy Duty
Chemical System:	Leclanché Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	ANSI-1604D, IEC-6F22
Nominal Voltage:	9.0 volts
Operating Temp:	-5°C to 55°C (20°F to 130°F)
Typical Weight:	37.0 grams (1.3 oz.)
Typical Volume:	20.3 cubic centimeters (1.2 cubic inches)
Jacket:	Metal
Terminal:	Miniature Snap

Milliamp-Hours Performance

Continuous discharge to 4.8 volts at 21°C



Industry Standard Tests (21°C)



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Energizer:

[1222 BULK](#) [1222](#) [1222BP](#)