




1.CABLE:NO UL,28AWG(7/0.127),TINNED AND STRANDED COPPER WIRE
INSULATOR:PVC,ID:0.85mm ,CABLING:9C+DRAIN WIRE
SHIELD:AL/MY COVERAGE

JACKET:PVC,COMPLIANCE ROHS,COLOR:BEIGE,D.D:5mm

2.1PCS CONNECTOR:D-SUB 9 WAYS MALE SOLDER TYPE CONNECTOR

INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE

CONTACT: COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED

SHELL:NICKEL PLATED.

CONNECTOR COMPLIANCE ROHS

3.1PCS CONNECTOR:D-SUB 9 WAYS FEMALE SOLDER TYPE CONNECTOR

INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE

CONTACT: COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED

SHELL:NICKEL PLATED.

CONNECTOR COMPLIANCE ROHS

4.HOOD:PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER

ON INNER MOLD AND INJECTION OUTER MOLD WITH

THUMB SCREW#4-40 UNC

COLOR:BEIGE,COMPLIANCE ROHS

5.Fulfil ROHS Guideline

6.ELECTRONIC TEST:100% OPEN SHORT+MISS WIRE TEST

PIN OUT

DB9PIN MALE(P1)	WIRE	DB9PIN FEMALE(J1)
1		1
2		2
3		3
4		4
5		5
6		6
7		7
8		8
9		9
SHELL	DRAIN WIRE	SHELL

PART NO	SHEET NO	1	THIRD ANGLE PROJECTION
TITLE: DB9 PIN MALE TO DB9 PIN FEMALE BEIGE COLOR	SCALE	N.T.S	DRAWN BY & DATE
	SIZE	A4	CHECKED BY & DATE
	UNIT		APPROVED BY & DATE
DWN NO		MM INCH	