




AD8025(T) SERIES

External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1007AWG24

Specifications(Nominal)


*Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
80x80x25	AD0812DB-A76GL(LTC)	◎ ※ ●	12	0.05	0.60	1600	0.611 21.607	0.046 1.168	14.0	86.0
	AD0812LB-A76GL(LTC)	◎ ※ ●	12	0.08	0.96	2100	0.803 28.387	0.075 1.905	22.1	
	AD0812MB-A76GL(LTC)	◎ ※ ●	12	0.12	1.44	2500	0.950 33.400	0.117 2.971	28.3	
	AD0812HB-A76GL(LTC)	◎ ※ ●	12	0.21	2.52	3000	1.139 40.259	0.154 3.911	33.4	
	AD0812UB-A76GL(LTC)	◎ ※ ●	12	0.23	2.76	3400	1.305 46.132	0.201 5.105	38.5	
	AD0824LB-A76GL(LTC)	◎ ※ ●	24	0.04	0.96	2100	0.803 28.387	0.075 1.905	22.1	
	AD0824MB-A76GL(LTC)	◎ ※ ●	24	0.07	1.68	2500	0.950 33.400	0.117 2.971	28.3	
	AD0824HB-A76GL(LTC)	◎ ※ ●	24	0.10	2.40	3200	1.244 43.987	0.178 4.521	35.4	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝！！)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓					✓					

*Safety approvals

UL	cUL	SP	CE	CE
✓	✓	✓	✓	✓