

3M™ Plain Cable Tie PB15BK50-C

The 3M™ Plain Cable Tie PB15BK50-C is 15" in length. Black color. 50 lb tensile strength. 100 per bag. (Replaces product number: 41977)

3M Id : 80-6114-7008-1

GTIN(UPC/EAN) : 0 00 51128 59349 3

Characteristics

Agency Approvals	UL
Cable Length	14.6 Inch
Cable Length (mm)	370.84 mm
Color	Black
Country of Origin	USA
EU RoHS Compliant	Yes
Indoor/Outdoor	Indoor
Maximum Bundle Diameter	4 Inch
Maximum Bundle Diameter (mm)	101.6 mm
Maximum Operating Temperature	85 Degree Celsius
Maximum Operating Temperature (Celsius)	85 Degree Celsius
Maximum Operating Temperature (Fahrenheit)	185 Degree Fahrenheit
Mil Spec	MS3367-2-0
Minimum Bundle Diameter	0.0625 Inch
Minimum Bundle Diameter (mm)	1.6 mm
Tensile Strength	50 Pound
Tensile Strength (kg)	22.67962 Kilogram
Thickness	0.054 Inch
Thickness (mm)	1.4 mm
Width	0.18 Inch
Width (mm)	4.6