



PRODUCT FINDER

- ▶ [Large Cabinet Racks](#)
- ▶ [Communications Cabinets/Racks](#)
- ▶ [Cabinets](#)
- ▶ [Open Racks](#)
- ▶ [Server Racks](#)
- ▶ [Aluminum Enclosures and Chassis](#)
- ▶ [Small Metal Enclosures](#)
- ▶ [Die Cast Boxes](#)
- ▶ [Plastic Enclosures](#)
- ▶ [NEMA Boxes \(Water-tight Plastic and Fiberglass\)](#)
- ▶ [NEMA Boxes \(Water-tight Sheet Metal\)](#)
- ▶ [NEMA Boxes \(Water-tight Aluminum\)](#)
- ▶ [Accessories](#)
- ▶ [Brackets](#)
- ▶ [Custom Enclosures](#)

Follow BUD On:



NEMA 4 Enclosures

SNB Series NEMA Sheet Metal Boxes



Click on Image for Larger View

Designed to meet NEMA 1, 2, 4, 4X, 12, 13 and IP66 ratings. UL listed and tested to UL508-4X, UL meets UL50E requirements

NEW!! Additional large size boxes, with enhanced design and continuous gasket (^) for superior performance.

[CLICK HERE TO VIEW A VIDEO](#)

Design Features

- Continuous seam welded 16 ga. steel or [stainless steel](#) construction
- Hinged cover clamps to the base with keyed quarter turn latch for a watertight seal
- External mounting brackets allow box to be mounted on a wall or panel without having to remove the cover and exposing internal components to the environment
- Bonding studs for grounding are provided on base and door
- Internal panel and hardware included
- UL Listed Type 1, 2, 4, 4X and 12. IP65 and IP66 ratings
- Easily machined and modified to your particular requirements
- Finish: Smooth Gray powder coat, Internal Panel - Clear Zinc plate

New Design features(^)

- Rigid door design
- Continues gasket
- Bar folded flange to enhance seal performance
- Additional rubber washer inside mounting brackets to enhance water resistant seal
- Added locks in larger size enclosures

SNB SERIES NEMA 4 SHEET METAL BOX WITH MOUNTING BRACKETS

Catalog Number	External Dimensions (Base)	Wall Mounting Dimensions	Internal Panel Dimensions	Wgt.	304 Stainless Steel Version
Drawings					

Powder Coated Steel		Height	Width	Depth	Height	Width	Height	Width	Lbs.	Catalog Number	Details
SNB-3730	PDF DXF	9.84"	7.87"	5.91"	11.14"	6.42"	8.46"	5.91"	7	SNB-3730-SS	Click Here
SNB-3731	PDF DXF	11.81"	9.84"	5.91"	13.11"	8.39"	10.43"	7.87"	9	SNB-3731-SS	Click Here
SNB-3732	PDF DXF	11.81"	9.84"	7.87"	13.06"	8.39"	10.43"	7.87"	11	SNB-3732-SS	Click Here
SNB-3733	PDF DXF	11.81"	11.81"	5.91"	13.11"	10.35"	10.43"	9.84"	11	SNB-3733-SS	Click Here
SNB-3734	PDF DXF	11.81"	11.81"	7.87"	13.11"	10.35"	10.43"	9.84"	12	SNB-3734-SS	Click Here
SNB-3735	PDF DXF	15.75"	11.81"	5.91"	17.05"	14.29"	14.37"	9.84"	15	SNB-3735-SS	Click Here
SNB-3736	PDF DXF	15.75"	11.81"	7.87"	17.05"	14.29"	14.37"	9.84"	16	SNB-3736-SS	Click Here
SNB-3737	PDF DXF	15.75"	15.75"	7.87"	17.05"	14.29"	14.37"	13.78"	22	SNB-3737-SS	Click Here
SNB-3738	PDF DXF	7.87"	5.91"	5.91"	9.17"	4.46"	6.49"	3.94"	5.2	SNB-3738-SS	Click Here
SNB-3739	PDF DXF	7.87"	7.87"	3.98"	9.17"	6.42"	6.49"	5.91"	4.6	SNB-3739-SS	Click Here
SNB-3740	PDF DXF	9.84"	9.84"	5.91"	11.14"	8.39"	8.46"	7.87"	9.7	SNB-3740-SS	Click Here
SNB-3741	PDF DXF	9.84"	7.87"	3.98"	11.14"	6.42"	8.46"	5.91"	5.7	SNB-3741-SS	Click Here
SNB-3743	PDF DXF	15.75"	13.98"	7.87"	17.05"	12.53"	14.37"	12.01"	19.8	SNB-3743-SS	Click Here
SNB-3746 ^	PDF DXF	20"	16"	8"	21.27	14.54	18.62	14.03	20.3	SNB-3746-SS	Click Here
SNB-3749 ^	PDF DXF	20"	20"	12"	21.27	18.54	18.62	18.03	29.4	SNB-3749-SS	Click Here
SNB-3751 ^	PDF DXF	24"	16"	8"	25.27	14.54	22.62	14.03	23.5	SNB-3751-SS	Click Here
SNB-3752 ^	PDF DXF	24"	20"	8"	25.27	18.54	22.62	18.03	27.8	SNB-3752-SS	Click Here
SNB-3754 ^	PDF DXF	24"	24"	10"	25.27	22.54	22.62	22.03	35.3	SNB-3754-SS	Click Here
* New sizes ^ New Design											

[DXF](#) Autocad DXF Specifications File

[PDF](#) Adobe PDF Specifications File

(Right Click and save link to your computer. Requires CAD software such as AutoCAD)



[Download PDF Viewer](#)

For the majority of our enclosures we offer 3D STEP files upon request

