


DC Power Jack

163-4019-EX

KOBI CONN

DC Power Jack



SPECIFICATIONS

Terminal:	silver plated brass
Pin:	nickel plated brass
Jack body:	PBT/GT resin
Rating:	6VDC, 2A
Insertion force:	500 ~ 1200gm
Extraction force:	400 ~ 1300gm
Contact resistance:	not more than 30mΩ
Insulation resistance:	not less than 100MΩ
Withstand voltage:	250VAC (50 ~ 60Hz) for one min.
Temperature range:	-20 °C ~ 70 °C
Life test:	5,000 times a min.
RoHs Compliant by Exemption	

Date Last Revised: 12-27-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300944

163-4019-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[163-4019-EX](#)