

Lamps

Lightbulb Type LED Lamps

Customize the mood with
ROHM lightbulb LED lamps

Wide distribution light lightbulb that mounted an LED in a solid substrate. A light similar to traditional lightbulb is obtained even if used in lighting devices for lightbulb. There are wide distribution light type and general type and two kinds of daylight white and lightbulb color can be chosen of each. We will deliver the emotion of LED that is produced from advanced technology.



Lightbulb Type LED Lamps


R-B101N1

Daylight White


6W Standard Type

Power	6W
Consumption	
Luminous Flux	335lm
Ra	70
Input Voltage	AC100V
Weight	110g
Cap/Base	E26
Illuminance (Directly Under)	55lx
Lifespan	40,000h

*Dimming not supported.

External Dimensions
(Unit: mm)

Property of light distribution

Seamless LED
Lighting

- ▶ Lineup
- ▶ Installation Example

Wall Washers

- ▶ Lineup

Downlights

- ▶ Lineup
- ▶ Installation Example

Slim Lights

- ▶ Lineup

Fluorescent Tube
Type LED Lamps

- ▶ Lineup

Lightbulb Type
LED Lamps

- ▶ Lineup

Modules

- ▶ Lineup

Lightbulb Type LED Lamps list

Product	Specifications			Emission Color	
	Power Supply	Power Consumption (W)	Cap/Base	 Daylight White	 Incandescent
Lightbulb Type LED Lamps	Diffuse Type	6W	E26	 R-B10N1	 R-B10L1
		8W	E26	 R-B15N1	 R-B15L1
	Standard Type	6W	E26	 R-B101N1	 R-B101L1

[To top of page ▲](#)[TOP](#) | [Products](#) | [Casae Studies](#) | [Technology](#) | [LED Lighting Lecture](#) | [Inquiries](#)

Copyright (C) 1997-2011 ROHM Co., Ltd.