




# 1008 Series

## D-SUB Right Angle Type





( ROHS )



5.08mm Footprint

### Dimensions

| Positions | A     | B     | C     | D     | E     |
|-----------|-------|-------|-------|-------|-------|
| 9         | 30.81 | 24.99 | 16.92 | 16.33 | 11.08 |
| 15        | 39.14 | 33.32 | 25.50 | 24.66 | 19.39 |
| 25        | 53.04 | 47.04 | 38.96 | 38.38 | 33.24 |
| 37        | 69.32 | 63.50 | 55.42 | 54.84 | 49.86 |




7.2mm ( 0.318" ) Footprint

# 1008 SERIES

## D-SUB RIGHT ANGLE TYPE

### How to order



### D-SUB CONNECTORS RIGHT ANGLE MOUNTING OPTIONS

