



ATQ224 | TQ Relays



Product name	TQ Relays
Product name detail	2-coil latch,PCB, Thru-hole,24V DC
Part Number	ATQ224
Product Number	TQ2-L2-24V
Series	TQ Relays

*Photo may vary from actual product.

RoHS Compliant Lead Free

Spec Detail

As of August 28, 2012

Item	Specifications
Part Number	ATQ224
Features	1,500V FCC, 4 pole model available.
Protective construction	Sealed
Terminal shape	PCB, Thru-hole
Foreign standards	UL/CSA
Coil voltage(V DC)	24
Nominal Operating Power	300mW
Pick-up voltage	-
Drop-out voltage	-
Nominal switching capacity (resistive load)	0.5A AC/1A DC,125V AC/30V DC
Min. switching capacity	10microA 10mV DC
Contact arrangement	2c
Contact material	BBM
Contact material	Ag(Au clad)
Max.switching current	1A
Mechanical life(Min.operation)	1x10 ⁶
Electrical life	2x10 ⁶
Rated voltage (Contact-Contact)	750Vrms
Rated voltage (Contact-Coil)	1000Vrms
Ambient temperature	-40deg to +70deg
Operating function	2 coil latching
Packing style	STICK

© Panasonic Corporation 2012