




NOTES

- 1. Material: SS 7030 (Zamak 5)
- 2. Packaging see GS-14-639
- 3. Surface treatment tin electroplating: min. 4 micron Cu, min. 6 micron Ni, 1: min. 6 micron Sn Bright + passivation.

4-ROHS INFORMATIONS:

- This product meets European Union Directives and other country regulations as described in GS-22-008.
- Packaging spec: see GS-14-920.

rev	ecn no	dr	date
A	LS4129	-	-
B	LS06-0084	LGO	2006/06/22
C	LS07-0001	MPE	2007/01/04
D	LS08-0024	LGO	2008/01/23
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	J. TARON	15/12/04	ANGULAR	LINEAR	0.X		±0.3		size A2	Scale 1:1
Eng	J. TARON	2004/12/15			0.XX		±0.1			
Chr	P. LEGARE	2004/12/15			0° ±2°		0.XXX			
Appr	P. LEGARE	2004/12/15	Product family			SOFIX		ECN		LS08-0024
						Spec ref		RELEASED		
		title SOFIX				deg no 10009609_C		Rev. D		
		72 POS. SHIELDING COVER								
		catalog no		10009609-002		CUSTOMER		sheet 1 of 1		