

Search Results

- Evaluate
- FAQ's
- Design a Solution
- Catalog Cut Sheet
 - PDFLCB-10-L Pro
 - Part Drawings
 - PDFCopper Lug, ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) [Search Tips](#)

 **Text Search: 'LCB2-12-Q'**

Your search criteria matched only one product, shown below

LCB2-12-Q



- For Use with Stranded Copper Conductors
- Long barrel maximizes number of crimps and provides premium wire pull -out strength and electrical performance
 - Color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection
 - Enclosed barrel prevents corrosive material from entering barrel when used in harsh environments
 - Tin-plated to inhibit corrosion
 - UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with Panduit and specified competitor crimping tools and dies
 - UL Listed and CSA Certified for wide wire range -taking capability when crimped with Panduit ® Uni-Die™ Dieless Crimping Tools‡
 - **Tested by Telcordia– meets NEBS Level 3**
 - American Bureau of Shipping Approved

Note: These code conductor lugs are manufactured for use with AWG wire only.

	Part Number	LCB2-12-Q
	RoHS Compliancy Status	Compliant
	Part Description	One-hole, long barrel lug, #2 AWG wire, 1/2" stud hole.
	Product Type	Compression Connectors- Lugs
	Material	Tin-Plated Copper
	CSA Certified	Yes
	UL Listed	Yes
	Length (In.)	2.58
	Length (mm)	65.5
	Copper Conductor Size	#2 AWG
	Stud Hole Size (In.)	1/2
	Tongue Width (In.)	0.75
	Barrel Length (In.)	1.16
	Angle	Straight
	Barrel Length (mm)	29.5
	CE Compliant	No
	Clearance	0.60
	Clearance (mm)	15.2
	Figure No.	1
	Panduit Color Code	Brown
	Panduit Die Index No.	P33
	Pricing Description	Copper Comp. Lug, 1 hole, #2 awg, long barrel, 1/2" (12.7mm) stud
	Stud Hole Size (mm)	12.7
	Tongue Thickness	0.08
	Tongue Type	Standard
	Tongue Width (mm)	19.1
	Wire Strip Length (In.)	1 1/4
	Wire Strip Length (mm)	31.8
	Min. Order UOM	PC
	Min. Order Qty.	1
	Burndy Die Index No.	10
	T&B Die Index No.	33
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.