


Model HB Horizontal Stacking Banana Plug Patch Cord, Banana Plug Each End



FEATURES:

- Front and vertical stacking banana plug.
- Mates to standard banana jacks.
- Ideal for providing jumpers on chassis boxes

MATERIALS:

Conn: Extension Stacking Banana Plug

Material: Spring, Beryllium Copper per QQ-C-533, Berylco 25, Cond. HT.

Plug Body and Plug Jack: Brass, per QQ-B-626, Alloy 360, ½ hard.

Finish: Nickel plate per QQ-N-290 class 2 (.0002 min.).

Insulation: Polypropylene molded to plug body, plug jack and wire

Color: Matches color of wire.

Marking: "MODEL HB-XX"

Wire: 18 AWG, stranding 65 x 36 t.c., PVC insulated (.050 wall thickness).

Color: See Ordering Information

Marking: "POMONA HB-XX-*)"

RATINGS: (Entire Assembly)

Operating Temperature: +55°C. (+131°F.) Max.

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 5000 WVDC Max.

Current: 15 Amperes Cont.

Contact Res.: Less than .001 Ohms per Banana Plug

ORDERING INFORMATION: Model HB-XX-*

XX = Cable Lengths, Standard Lengths: 12" (305), 24" (610), 36" (914), 48" (1219)

Additional lengths can be quoted upon request.

*= Color, -0 Black, -2 Red. Ordering Example: HB-48-2 Indicates 48" in length, color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA