

NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: XELCOLOR

HOUSING & PLUNGER & SLIDE: MOLDED NYLON 6,6.
AVAILABLE IN TEN COLORS.

CONTACT NEEDLE: STAINLESS STEEL.
BANANA SOCKER: 360 1/2 HD. BRASS.
COMPRESSION SPRING: STAINLESS STEEL.

2. P/N: 9214COLOR


HOUSING: MOLDED ACETAL. AVAILABLE IN BLACK OR RED.
FRAME: BRASS. NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.

3. P/N: W-600/COLOR

18AWG 65X36 TINNED COPPER
0.144 [3.66] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

4. PERFORMANCE

MAXIMUM CURRENT: 4.0 AMPS
MAXIMUM VOLTAGE: 5000 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		CONTRACT NO.	
		±	.XX ±	±	APPROVALS
			.XXX ±		DATE
		MATERIAL		DRAWN	R.L
		SEE NOTE.		APPROVED BY	9/10
		FINISH			
		SEE NOTE.			
		NEXT ASSY			
		USED ON			
		APPLICATION		DO NOT SCALE DRAWING	

E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.			REVISIONS		DATE	APPROVED
DESCRIPTION			LTR	DESCRIPTION	DATE	APPROVED
MACRO-HOOK (XEL) TO STD BANANA PLUG (9214)						
SIZE	CODE IDENT NO.	DRAWING NO.				REV.
B	08505	BXEL				
SCALE	1:1				SHEET 1 OF 1	