








1. HOUSING: PBT, 30% GF POLYESTER, UL 94V-O RATED, COLOR BLACK.
2. CONTACTS: PHOSPHOR BRONZE, GOLD PLATE IN MATING AREA (SEE TABLE), 120u" MIN TIN PLATE ON SOLDER TAIL, BOTH OVER 50u" MIN NICKEL UNDERPLATE.
3. SHELL: STEEL, NICKEL PLATE.
4. BOARDLOCK: BRASS, TIN PLATE 100u" MIN.
5. FEMALE SCREWLOCK: BRASS, NICKEL PLATE 30u" MIN.
6. FOUR DIGIT DATE CODE IN THIS FORMAT.

YEAR — 01 — 45 — MANUFACTURING WEEK

7 DATUMS -X- & -Y- TO BE ESTABLISHED BY CUSTOMER.




SEE TABLE FOR
MOUNTING FLANGE
CONFIGURATION



Detail A

Detail B



BOARDLOCK
2 PLC
(SEE TABLE)

OBSOLETE	NO	Tray	Detail B	Gold flash	2-5748481-7
OBSOLETE	NO	Tray	Detail B	15μ" MIN GOLD	2-5748481-6
OBSOLETE	YES	Tray	Detail A	Gold flash	2-5748481-5
OBSOLETE	YES	Tray	Detail A	15μ" MIN GOLD	2-5748481-4
OBSOLETE	YES	Tray	Detail B	Gold flash	2-5748481-3
OBSOLETE	YES	Tray	Detail B	15μ" MIN GOLD	2-5748481-2
OBSOLETE	NO	Tray	Detail B	30μ" MIN GOLD	1-5748481-9
	YES	Tray	Detail A	30μ" MIN GOLD	5748481-6
	YES	Tray	Detail B	30μ" MIN GOLD	5748481-5
	BOARDLOCK	Packaging	Mounting Flange	Contact Mating Area Finish	Part No

THIS DRAWING IS A CONTROLLED DOCUMENT.

T.	DWN R. RICHARDSON
----	----------------------

31MAY05

ET

TE Connectivity

AMPLIMITE HD-22
26 POS RECEPTACLE, RIGHT ANGLE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED
------	-----------	------------	------------

A2 00779 ©=5748481

SCALE	1:1	SHEET	1 OF 1	REV	DC
-------	-----	-------	--------	-----	----

1471-9 (3/11)

5748481-5, 2--2, & 2--3 SHOWN