





PART NO.	"A" [IN.] MIN.	"B" +/- .062 [IN.]	"C" +/- .05 [IN.]	MATERIAL	COLOR
T100X000RXI	600	1.00	0.125	GMRS, GMY4-C	YELLOW REFLECTIVE
T200X000RXI	600	2.00	0.125	GMRS, GMY4-C	YELLOW REFLECTIVE
T400X000RXI	600	4.00	0.125	GMRS, GMY4-C	YELLOW REFLECTIVE
T100X000RU1	600	1.00	0.125	GMRS, GMY4-C	ORANGE REFLECTIVE
T200X000RU1	600	2.00	0.125	GMRS, GMY4-C	ORANGE REFLECTIVE
T400X000RU1	600	4.00	0.125	GMRS, GMY4-C	ORANGE REFLECTIVE
T100X000RP1	600	1.00	0.125	GMRS, GMY4-C	WHITE REFLECTIVE
T200X000RP1	600	2.00	0.125	GMRS, GMY4-C	WHITE REFLECTIVE
T300X000RP1	600	2.00	0.125	GMRS, GMY4-C	WHITE REFLECTIVE
T400X000RP1	600	4.00	0.125	GMRS, GMY4-C	WHITE REFLECTIVE
T200X000RW1	600	2.00	0.125	GMRS, GMY4-C	RED REFLECTIVE
T400X000RW1	600	4.00	0.125	GMRS, GMY4-C	RED REFLECTIVE
T400X000RO1	600	4.00	0.125	GMRS, GMY4-C	BLUE REFLECTIVE



NOTES:
1. RESIN RIBBON
RECOMMENDED.

CAD FILENAME/LAYERS										I00923NX-DC-C10750/01D	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										CUSTOMER DRAWING T***X000R** REFLECTIVE THERMAL TRANSFER CONTINUOUS TAPES	
3	11/5/13	JHAC		ADD T200X000RW1 ON TABLE.	GAECN01353	R				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1 (.XXX) ± .02 (.XX) ± .050 ANGLES ± 5°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
2	9/2/11	RVU		ADD T300X000RP1 ON TABLE.	6493	R					
1	12/15/08	JHAC		DRAWING RELEASED.	5627	R				DRAWN BY ACCH	MAT'L; SEE TABLE
0	11/12/08	ACCH		VOID		R				DATE 11/12/08	DRAWING NO. C10750
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D	DWG A SIZE