




2002-07-08

## **PRODUKTINFORMATION**

Vi reserverar oss mot fel samt förbehåller oss rätten till ändringar utan föregående meddelande


**ELFA artikelnr**

**69-210-19 Batteri Zink-luft DA10**



|                              |                                            |
|------------------------------|--------------------------------------------|
| Nominal Voltage:             | 1.4 V                                      |
| Rated Capacity:              | 90 mAh at 3000 ohm to 1.1 V at 21°C (70°F) |
| Nominal Internal Impedance:  | 16 ohm @ 1kHz                              |
| Average Weight:              | 0.3 gm                                     |
| Volume:                      | 0.06 cm <sup>3</sup>                       |
| Terminals:                   | Flat                                       |
| Operating Temperature Range: | 0°C to 50°C (32°F to 122°F)                |
| ANSI:<br>IEC:                | 7005 ZD<br>PR70                            |

Typical Discharge Characteristics at 21°C (70°F)



**DURACELL®**  
BATTERIES

Berkshire Corporate Park  
Bethel, CT 06801 U.S.A.

Internet: [www.duracell.com](http://www.duracell.com)  
Telephone: Toll-free 1-800-544-5454

\* \* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.