

SUPER MICRO CONNECTORS

SERIES


5046

プラグ(H=3.0mm)



Plug (H=3.0mm)

金具無 without metal


金具付 with metal





極数 NO. OF POS.	A	B
20	4.5	8.1
30	7.0	10.6
40	9.5	13.1
50	12.0	15.6
60	14.5	18.1
70	17.0	20.6
80	19.5	23.1
90	22.0	25.6
100	24.0	28.1
110	27.0	30.6
120	29.5	33.1



極数 NO. OF POS.	A	B	C
20	4.5	10.5	7.7
30	7.0	13.0	10.2
40	9.5	15.5	12.7
50	12.0	18.0	15.2
60	14.5	20.5	17.7
70	17.0	23.0	20.2
80	19.5	25.5	22.7
90	22.0	28.0	25.2
100	24.5	30.5	27.7
110	27.0	33.0	30.2
120	29.5	35.5	32.7



嵌合高さ
STACKING HEIGHT
H=3mm TYPE



注文コード Ordering Code

嵌合高さ STACKING HEIGHT	型番 P/N					
3.0mm	FEMALE	24	5046	XXX	X00	829
	MALE	14	5046	XXX	X30	829

極数 NO. OF POS.	寸法 DIMENSION B
020	10.5
030	13.0
040	15.5
050	18.0
060	20.5
070	23.0
080	25.5
090	28.0
100	30.5
110	33.0
120	35.5

VARIATION CODE

0	金具無 WITHOUT METAL
1	金具付 WITH METAL
5	金具無 吸着テープ付 WITHOUT METAL, WITH VACUUM TAPE
6	金具付 吸着テープ付 WITH METAL, WITH VACUUM TAPE

SUPER MICRO CONNECTORS


SERIES

5046


プラグ(H=3.5mm)

Plug (H=3.5mm)

金具無 without metal




極数 NO. OF POS.	A	B
20	4.5	8.1
30	7.0	10.6
40	9.5	13.1
50	12.0	15.6
60	14.5	18.1
70	17.0	20.6
80	19.5	23.1
90	22.0	25.6
100	24.0	28.1
110	27.0	30.6
120	29.5	33.1




基板取付け寸法
MOUNTING LAYOUT

金具付 with metal





極数 NO. OF POS.	A	B	C
20	4.5	10.5	7.7
30	7.0	13.0	10.2
40	9.5	15.5	12.7
50	12.0	18.0	15.2
60	14.5	20.5	17.7
70	17.0	23.0	20.2
80	19.5	25.5	22.7
90	22.0	28.0	25.2
100	24.5	30.5	27.7
110	27.0	33.0	30.2
120	29.5	35.5	32.7



基板取付け寸法
MOUNTING LAYOUT

注文コード Ordering Code

嵌合高さ
STACKING HEIGHT
H=3.5mm TYPE



嵌合高さ STACKING HEIGHT	型番 P/N
3.5mm	FEMALE 24 5046 XXX X00 829 MALE 14 5046 XXX X35 829

極数 NO. OF POS.	寸法 DIMENSION B
020	10.5
030	13.0
040	15.5
050	18.0
060	20.5
070	23.0
080	25.5
090	28.0
100	30.5
110	33.0
120	35.5

VARIATION CODE

0	金具無 WITHOUT METAL
1	金具付 WITH METAL
5	金具無 吸着テープ付 WITHOUT METAL, WITH VACUUM TAPE
6	金具付 吸着テープ付 WITH METAL, WITH VACUUM TAPE

SUPER MICRO CONNECTORS


SERIES

5046


プラグ(H=4.0mm)

Plug (H=4.0mm)

金具無 without metal




極数 NO. OF POS.	A	B
20	4.5	8.1
30	7.0	10.6
40	9.5	13.1
50	12.0	15.6
60	14.5	18.1
70	17.0	20.6
80	19.5	23.1
90	22.0	25.6
100	24.0	28.1
110	27.0	30.6
120	29.5	33.1




基板取り付け寸法
MOUNTING LAYOUT

金具付 with metal





極数 NO. OF POS.	A	B	C
20	4.5	10.5	7.7
30	7.0	13.0	10.2
40	9.5	15.5	12.7
50	12.0	18.0	15.2
60	14.5	20.5	17.7
70	17.0	23.0	20.2
80	19.5	25.5	22.7
90	22.0	28.0	25.2
100	24.5	30.5	27.7
110	27.0	33.0	30.2
120	29.5	35.5	32.7



基板取り付け寸法
RECOMMENDED LAYOUT

注文コード Ordering Code

嵌合高さ
STACKING HEIGHT
H=4mm TYPE



嵌合高さ STACKING HEIGHT	型番 P/N
4.0mm	FEMALE 24 5046 XXX X00 829 MALE 14 5046 XXX X40 829

極数 NO. OF POS.	寸法 DIMENSION B
020	10.5
030	13.0
040	15.5
050	18.0
060	20.5
070	23.0
080	25.5
090	28.0
100	30.5
110	33.0
120	35.5

VARIATION CODE

0	金具無 WITHOUT METAL
1	金具付 WITH METAL
5	金具無 吸着テープ付 WITHOUT METAL, WITH VACUUM TAPE
6	金具付 吸着テープ付 WITH METAL, WITH VACUUM TAPE


SERIES

5046


プラグ(H=4.5mm)

Plug (H=4.5mm)

金具無 without metal




NO. OF PSS	A	B
20	4.5	8.1
30	7.0	10.6
40	9.5	13.1
50	12.0	15.6
60	14.5	18.1
70	17.0	20.6
80	19.5	23.1
90	22.0	25.6
100	24.0	28.1
110	27.0	30.6
120	29.5	33.1




基板取付け寸法

MOUNTING LAYOUT

金具付 with metal



No. of Pops	A	B	C
20	4.5	10.5	7.7
30	7.0	13.0	10.2
40	9.5	15.5	12.7
50	12.0	18.0	15.2
60	14.5	20.5	17.7
70	17.0	23.0	20.2
80	19.5	25.5	22.7
90	22.0	28.0	25.2
100	24.5	30.5	27.7
110	27.0	33.0	30.2
120	29.5	35.5	32.7





MOUNTING LAYOUT

注文コード Ordering Code

嵌合高さ STACKING HEIGHT	型番 P / N						
4.5mm	EMALE	24	5046	XXX	X00	829	
	MALE	14	5046	XXX	X45	829	

積合高さ
STACKING HEIGHT
H=4.5mm TYPE



極数 NO. OF POS.	寸法 DIMENSION
	B
020	10.5
030	13.0
040	15.5
050	18.0
060	20.5
070	23.0
080	25.5
090	28.0
100	30.5
110	33.0
120	35.5

VARIATION CODE



0	金具無 WITHOUT METAL
1	金具付 WITH METAL
5	金具無 吸着テープ付 WITHOUT METAL, WITH VACUUM TAPE
6	金具付 吸着テープ付 WITH METAL, WITH VACUUM TAPE

SUPER MICRO CONNECTORS

SERIES


5046

プラグ エンボス(H=3.0, 3.5, 4.0, 4.5mm)
Plug Tape and Reel Package (H=3.0, 3.5, 4.0, 4.5mm)



HEIGHT	G
H=3.0	4.1
H=3.5	4.1
H=4.0	4.6
H=4.5	4.6

	極数 NO. OF POS.	A	B	C	D
32mm TAPE	20	8.1	26.5	28.4	32.0
	30	10.6			
	40	13.1			
	50	15.6			
	60	18.1			
44mm TAPE	70	20.6	38.5	40.4	44.0
	80	23.1			
	90	25.6			
	100	28.1			
56mm TAPE	110	30.6	50.5	52.4	56.0
	120	33.1			



HEIGHT	G
H=3.0	4.1
H=3.5	4.1
H=4.0	4.6
H=4.5	4.6

	極数 NO. OF POS.	A	B	C	D
32mm TAPE	20	8.1	26.5	28.4	32.0
	30	10.6			
	40	13.1			
	50	15.6			
	60	18.1			
44mm TAPE	70	20.6	38.5	40.4	44.0
	80	23.1			
	90	25.6			
	100	28.1			
56mm TAPE	110	30.6	50.5	52.4	56.0
	120	33.1			


SUPER MICRO CONNECTORS

SERIES


5046

リセ
Receptacle

金具無 without metal




極数 NO. OF POS.	A	B
20	4.5	8.1
30	7.0	10.6
40	9.5	13.1
50	12.0	15.6
60	14.5	18.1
70	17.0	20.6
80	19.5	23.1
90	22.0	25.6
100	24.5	28.1
110	27.0	30.6
120	29.5	33.1




基板取付け寸法
MOUNTING LAYOUT

金具付 with metal



極数 NO. OF POS.	A	B	C
20	4.5	10.5	7.7
30	7.0	13.0	10.2
40	9.5	15.5	12.7
50	12.0	18.0	15.2
60	14.5	20.5	17.7
70	17.0	23.0	20.2
80	19.5	25.5	22.7
90	22.0	28.0	25.2
100	24.5	30.5	27.7
110	27.0	33.0	30.2
120	29.5	35.5	32.7



基板取付け寸法
MOUNTING LAYOUT

注文コード Ordering Code

嵌合高さ STACKING HEIGHT		型番 P/N
4.5mm	FEMALE	24 5046 XXX X00 829
	MALE	14 5046 XXX X45 829
4.0mm	FEMALE	24 5046 XXX X00 829
	MALE	14 5046 XXX X40 829
3.5mm	FEMALE	24 5046 XXX X00 829
	MALE	14 5046 XXX X35 829
3.0mm	FEMALE	24 5046 XXX X00 829
	MALE	14 5046 XXX X30 829

極数 NO. OF POS.	寸法 DIMENSION B
020	10.5
030	13.0
040	15.5
050	18.0
060	20.5
070	23.0
080	25.5
090	28.0
100	30.5
110	33.0
120	35.5

VARIATION CODE

0	金具無 WITHOUT METAL
1	金具付 WITH METAL
5	金具無 吸着テープ付 WITHOUT METAL. WITH VACUUM TAPE
6	金具付 吸着テープ付 WITH METAL. WITH VACUUM TAPE



SUPER MICRO CONNECTORS

SERIES



5046

リセ エンボス

Receptacle Tape and Reel Package



	極数 NO. OF POS.	A	B	C	D
32mm TAPE	20	10.65			
	30	13.15			
	40	15.65	26.5	28.4	32.0
	50	18.15			
	60	20.65			
44mm TAPE	70	23.15			
	80	25.65	38.5	40.4	44.0
	90	28.15			
	100	30.65			
56mm TAPE	110	33.15	50.5	52.4	56.0
	120	35.65			



	極数 NO. OF POS.	A	B	C	D
32mm TAPE	20	10.65			
	30	13.15			
	40	15.65	26.5	28.4	32.0
	50	18.15			
	60	20.65			
44mm TAPE	70	23.15			
	80	25.65	38.5	40.4	44.0
	90	28.15			
	100	30.65			
56mm TAPE	110	33.15	50.5	52.4	56.0
	120	35.65			