






FACE VIEW OF
END RECEPTACLE



NOTE
PINS 1,2,9,10,11,13,17,18 NOT USED

MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH	CABLE JACKET MATERIAL
1201140035	BTY4030-FBB	-	-

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	NYLON	BLACK
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	O-RING	NITRILE	RED
4	RECEPTACLE SHELL	BRASS	NICKEL PLATED
5	HOUSING	PBT	YELLOW
6	LABEL	ABS	WHITE

DESCRIPTION
EC NO: WEU2010-0423
DRWN: LSTEMMLE 2010/03/10
CHKD: NSTAUDIG
APPR: NSTAUDIG 2010/03/16

DESCRIPTION
REV

QUALITY SYMBOLS
= 0
= 0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±.01
1 PLACE	±0.3	±---
ANGULAR ± --- °		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY
LSTEMMLE

DATE
2010/03/10

CHECKED BY
FP

DATE
2010/03/10

APPROVED BY
NSTAUDIG

DATE
2010/03/15

MATERIAL NO.
SEE TABLE

SIZE
A3

SCALE
2:1

DESIGN UNITS
METRIC

THIRD ANGLE PROJECTION

MICRO-CHANGE MPIS
4 PORT TOP MOUNT
MINI-CHANGE

molex

MOLEX INCORPORATED

DOCUMENT NO.
SD-120114-023

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION