



Industrial Adhesives & Tapes

- Products
- Applications
- Industries
- Capabilities
- Support

Where to Buy

United States > All 3M Products > Market Segments > Manufacturing and Industry > Industrial Adhesives & Tapes > Adhesives - Wind > 3M™ Scotch-Weld™ Epoxy Potting Compound DP270 Clear, 400 mL, 6 per case

3M™ Scotch-Weld™ Epoxy Potting Compound DP270 Clear, 400 mL, 6 per case

3M ID 62326235306 UPC# 00021200878350 Part Number DP270 3M Product Number DP270

Print Share



3M™ Scotch-Weld™ Epoxy Potting Compound DP270 is a rigid, two-part epoxy adhesive potting compound. 1:1 mix ratio, 70 minute work life and handling strength in approximately 3 hours. 3M™ Scotch-Weld™ EPX™ 400 mL applicator and mix nozzles are required (not included).

- 70 minute worklife
- Non-corrosive to copper
- Rigid potting compound
- General industrial, sporting goods, solar energy, wind energy, composites, electronics, military, transportation and aerospace
- Bonding, gluing, joining, attaching, assembling, encapsulating, potting and sealing.

[Buy at Shop3M.com](#)

Need Help?

Questions? We can help [Contact Us](#)

- Overview
- Documents

3M™ Scotch-Weld™ Epoxy Potting Compound DP270 is low viscosity for easy dispensing and potting. Non-corrosive to copper, non-exotherming and high flow. For potting and bonding electronic and electrical components.

Specifications

Applications	Hard Disk Drive Component Assembly
Brand	Scotch-Weld
Chemical Base	Epoxy
Color	Clear
Container Volume	400 ml
Full Cure	48 Hours @ 72 F (22 C)
Hardness	80 Shore D
Industries	General Industrial, Construction, Electronics, Specialty Vehicle, Transportation, Consumer Goods, Military & Government
Mix Ratio Volume Base:Accelerator	1 : 01
Peel Strength at 72 Degrees F (22 Degrees C)	2 Pound Per Inch (Of Width)
Physical Form	Liquid
Product Form	Each
Shear Strength at 72 Degrees F (22 Degrees C)	2500 Pound-Force Per Square Inch
Shelf Life	15 Months
Specific Gravity	1.06
Storage Temperature	72 Degree Fahrenheit
Substrate 1	Metal
Substrate 2	Metal
Time to Handling Strength	3 Hour
Type	Epoxy Adhesive
Viscosity Range (cps) at Room Temperature	12,000
Worklife	70 minutes @ 72 F (22 C)

