





### Features:

- Size: 1.57" x .79" wide (40mm x 20mm)
- Air Flow: 7.5-10 CFM
- Noise: 25-31.9 dBA
- Operating Voltage: 5, 12, & 24 vdc
- Operating Temperature: -10°C to +70°C
- Storage Temperature: -40°C to +75°C
- Weight: .07 lb (34 g)
- Agencies: UL, CUR, TUV, CE
- Ball Bearing Unit: (Sleeve Bearing Available)



| Model No.       | Part No. | Voltage Nominal (VDC) | Running Current (amps) | Power (Watts) | RPM  | CFM  | Static Pressure | Noise (dBA) |
|-----------------|----------|-----------------------|------------------------|---------------|------|------|-----------------|-------------|
| CR0405HB-C50    | 032616   | 5                     | .200                   | 1.00          | 7800 | 10.0 | .256            | 31.9        |
| CR0405MB-C50    | 032618   | 5                     | .160                   | .80           | 6900 | 8.5  | .190            | 28.5        |
| CR0405LB-C50    | 032620   | 5                     | .140                   | .70           | 6000 | 7.5  | .160            | 25.0        |
| * CR0412HB-C50  | 032622   | 12                    | .100                   | 1.20          | 7800 | 10.0 | .256            | 31.9        |
| CR0412MB-C50    | 032624   | 12                    | .080                   | .96           | 6900 | 8.5  | .190            | 28.5        |
| CR0412LB-C50    | 032626   | 12                    | .070                   | .84           | 6000 | 7.5  | .160            | 25.0        |
| *† CR0424HB-C50 | 032628   | 24                    | .090                   | 2.16          | 7800 | 10.0 | .256            | 31.9        |
| † CR0424MB-C50  | 032630   | 24                    | .070                   | 1.68          | 6900 | 8.5  | .190            | 28.5        |

\* Distributor Item

† Agencies Vary (Consult Factory)

**Comair Rotron**

2675 Customhouse Court • San Ysidro CA 92173 • Ph (619) 661-6688 Fax (619) 661-1757

E-mail: sales@comairrotron.com • Web: www.comairrotron.com