

**Part Number: 92903-2205**

LaneLink™/ InfiniBand\* Direct Attach Cable Assembly, 12X, 26AWG, Jack Screws, 7.0m Length

Image not available

**Status:** **OBSOLETE**  
**Replacement:** [929032225](#)  
**Series:** [92903](#)  
**Category:** Cable Assemblies

Series image - Reference only

**Mates With Part(s):**[91629](#)**Product Environmental Compliance**

**EU RoHS:** Not RoHS Compliant  
**China RoHS:**   
**REACH SVHC:** Not Reviewed  
**Low-Halogen Status:** Not Reviewed

**Part Detail****General**

Status	Obsolete
Category	Cable Assemblies
Series	<a href="#">92903</a>
Connector to Connector	InfiniBand* 12x Both Ends
More Detailed Tech Information	LaneLink™/ InfiniBand* Direct Attach Cable Asse.0mbly, 12X, 26AWG, Jack Screws, 7.0m
Obsolete Date	2004/11/01
Product Name	12X, InfiniBand*, LaneLink™

**Physical**

Cable Length	7.0m
Circuits (Loaded)	12X
Gender	Female-Female
Lock to Mating Part	Yes
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Single Ended	No
Wire Size AWG	26
Wire/Cable Type	Parallel Pair

**Electrical****(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.5A
Impedance	100Ω
Shielded	Yes
Voltage - Maximum	30V AC

**Material Info**

UPC	756054811719
-----	--------------

**Reference - Drawing Numbers**

Packaging Specification	PK-92903-001
Product Specification	PS-91525-001
Sales Drawing	SD-92903-001

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)

