



SECTION A-A

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE AMERICANA
(THIRD ANGLE PROJECTION)1 Tolleranza non cumulativa
(Non-cumulative tolerance)

Nr. Pos.	Part Number	Dim "A"	Dim "B"	Dim "C"
5	284123-1	10.16	13.2	14.7
22	280369	53.34	56.4	57.9
18	281018	43.18	46.2	47.8
15	280368	35.56	38.6	40.1
12	280515	27.94	31	32.5
9	280513	20.32	23.3	24.9
8	280366	17.78	20.8	22.3
6	282792-1	12.7	15.7	17.2
4	280365	7.62	10.6	12.2

CUSTOMER DRAWING
FOR REFERENCE ONLYDISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE, SE NON
DIVERSAMENTE SPECIFICATOMATERIALI (MATERIALS)
NORYL (UL94-V1)SCALA
(SCALE)

Colore nero (Black colour)

AMP AMP ITALIA S.p.A.
Corso F.lli Cervi, 15
COLLEGNO (TORINO)Z RELEASED FOR PRODUCTION P/N 284123-1
PER ET00-0301-98

U1 MODIFIED PER ET00-0150-98 F.B. 19MAY 1998

U NOT YET RELEASED
FOR PRODUCTION P/N 284123-1
PER ET00-0112B RELEASED FOR PROD.
P/N 282792-1 (ET00-0452-96) C.P. 21-10 '96A -REDRAWN BY CAD
-ADDED 6x2 POSITION
PER ET00-0053-96 M.S. 5-2 '96

REV. (REVISION RECORD)

DIS. DATA (DATE)

TOLLERANZE, UNLESS
OTHERWISE SPECIFIED

± 0.3

ANGOLI (ANGLES) ± 2°

DIS. M. SCOMPARIN
(DR.) 2 JAN 96CONT. R. CANTORE
(CHK) 2 JAN 96

APP. (APP.)

DIS. DATA (DATE)

DESCRIZIONE (DESCRIPTION)

AMP MODU Mod. II Rec.

HSG, Double Row, Crimp Snap-in.

LOC. SIZE NUMERO (DWG NO)

I A3 C- 280365

REV. 1

FOGLIO (SHEET) D1 (OF) 1