




MATERIALS:

Body and Fittings: Brass per QQ-B-626, Alloy 360, ½ hard

Center Contacts: Gold Plated Beryllium Copper per QQ-C-530, Cond. HT.

Dielectric: PTFE

Finish:

Body and Fittings: Tarnish Resistant

Center Contacts: Gold plated per requirements of MIL-C-39012

Marking: "POMONA 4940"

RATINGS:

Operating Voltage: 500 VRMS

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 4940

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA