


Dimensions (In.)

Specifications:

- Type: 15mm carbon trimmer
- Taper: linear
- Power rating: .25W
- Voltage rating: 200V
- Rotational angle: $230^{\circ} \pm 20^{\circ}$
- Tolerance: $\pm 20\%$ (except 500K, $\pm 30\%$)
- Operating temperature: $-25^{\circ}\text{C} \sim +70^{\circ}\text{C}$
- Values: 300, 500, 1K, 3K, 5K, 10K, 30K, 50K, 100K, 300K, 500K, 1M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[320-1510-1MEG](#) [320-1510-5K](#) [320-1510-500K](#) [320-1510-1K](#) [320-1510-300](#) [320-1510-3K](#) [320-1510-100K](#) [320-1510-500](#)