



PANDUIT PART NUMBER	MAXIMUM CABLE DIAMETER	PANEL DIMENSIONS		WEIGHT LBS. (g) / 100 PCS
		THICKNESS	HOLE SIZE	
SICH38	.38 (9.7)	.03/.10 (0.8/2.5)	.250 (6.4)	.15 (69)

1. SEE CURRENT PRICE SHEET FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE
AND PART COLOR.

										(DIMENSIONS IN PARENTHESES ARE METRIC)	
										CAD FILENAME/LAYERS	
										G0239JL_PB_SICH38_00	
										 PANDUIT CORP. TINLEY PARK, ILLINOIS	
										SNAP-IN CLIP	
										SICH38	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± N/A (.XXX) ± .010 (.25) (.XX) ± .02 (.5) ANGLES ± N/A	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY LGG DATE 9-4-02 CHK'D	
										MAT'L: NYLON 6/6	
										SCALE 2/1 DRAWING NO. G0239JL DWG A SIZE	
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP
R	9-4-02	LGG		INITIAL RELEASE. REPLACED G-00841			G0239JL		R		