



Part Number : 5988320117F



5988320117F

[Share](#) | |

[Surface Mount LED Selector Guide](#)

General Description

Lens Color	Water Clear
Series	598
Description	SM LED 1208 ALINGAP 7 REEL
Package Options	7" reel 4,000pcs / reel
Viewing Angle	160°

Absolute Maximum Ratings (Ta = 25 °)

Forward Current mA	20mA
Reverse Voltage	5v
Operating Temperature	-40~+100 °C
Storage Temperature	-40~+100 °C

Operating Characteristics

Color	Red - Orange
Power Dissipation Max	48nW