



LOC	DIST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
G	86				T	REV PER 0G3A-0561-01	080CT02	JR/MS



1 CIRCULAR MIL AREA RANGE: 375-450 MCM
2 TIN PL 0.00381 [.000150] MIN THK PER MIL-T-10727



				PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75		DR 03/16/90 DK SCHRUM		AMP AMP INCORPORATED Harrisburg, Pa. 17105	
		CHK 23JAN95 MS FEHER			
		APPD 23JAN95 WJ VOCKROTH		NAME TERMINAL, AMPPOWER TM , WIRE SIZE: 400 MCM	
		APPD 23JAN95 TL SHUTTER			
FINISH 2		PRODUCT SPEC 108-30200			
		APPLICATION SPEC -		SIZE C	
		WEIGHT .231 LB		CAGE CODE 00779	
		SCALE 2:1		DRAWING NO 326003	
				SHEET 1 OF 1	