


Dimensions (In.)



Specifications:

- Type: economy encapsulated RF
- Operating temperature: -20°~+80°C
- Core: ferrite/iron
- Dielectric strength: 5KV for 1 minute
- Voltage rating: 800V
- Tolerance: 10%
- Test frequency: 252 KHZ

Mouser Stock No.	Inductance		Q Min.	Minimum Resonance Frequency	Current DC MA (Max.)	DC Resistance (Maximum)
	In uH	In mH				
43LH210	1000	1.0	60	1.40	250	2.5
43LH212	1200	1.2	75	1.30	250	3.0
43LH215	1500	1.5	75	1.10	150	5.0
43LH218	1800	1.8	75	1.00	150	5.5
43LH222	2200	2.2	75	0.90	150	7.0
43LH227	2700	2.7	75	0.80	150	8.0
43LH233	3300	3.3	75	0.70	150	9.0
43LH239	3900	3.9	75	0.68	100	10.0
43LH247	4700	4.7	60	0.65	100	11.5
43LH256	5600	5.6	60	0.56	100	15.0
43LH268	6800	6.8	45	0.45	100	16.8
43LH282	8200	8.2	45	0.40	50	19.5
43LH310	10000	10.0	80	0.35	50	34.0
43LH312	12000	12.0	80	0.33	50	39.0
43LH318	18000	18.0	80	0.30	50	50.0
43LH322	22000	22.0	80	0.25	50	57.0
43LH327	27000	27.0	80	0.20	50	70.0
43LH333	33000	33.0	80	0.19	50	75.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[43LH210](#) [43LH212](#) [43LH215](#) [43LH218](#) [43LH222](#) [43LH227](#) [43LH233](#) [43LH239](#) [43LH247](#) [43LH268](#) [43LH282](#)
[43LH310](#) [43LH322](#) [43LH327](#) [43LH333](#)