

# Wera Kraftform® Plus Series 100 VDE

## The safety screwdriver with a multi-component Kraftform® handle.

### 160 i VDE Insulated Slotted Screwdriver Kraftform® Plus



**Application:** For slotted screws  
**Blade:** Insulated  
**Tip:** DIN 5264-A, ISO 2380, conical tip, Lasertip®  
**Handle:** Kraftform® with anti-roll protection, multi-component  
**Standard:** IEC 60900 : 2004

| Code                      | mm  | mm   | mm  | mm  | mm      | mm     | mm | mm | mm |
|---------------------------|-----|------|-----|-----|---------|--------|----|----|----|
| 05006100001 <sup>1)</sup> | 0,4 | 2,5  | 80  | 81  | 3 1/32" | 3 1/8" |    |    | 10 |
| 05006105001 <sup>1)</sup> | 0,5 | 3,0  | 100 | 81  | 1/8"    | 4"     |    |    | 10 |
| 05006110001               | 0,6 | 3,5  | 100 | 81  | 9/64"   | 4"     |    |    | 10 |
| 05006115001               | 0,8 | 4,0  | 100 | 98  | 5/32"   | 4"     |    |    | 10 |
| 05006116001               | 0,8 | 4,0  | 150 | 98  | 5/32"   | 6"     |    |    | 10 |
| 05006120001               | 1,0 | 5,5  | 125 | 98  | 7/32"   | 5"     |    |    | 10 |
| 05006121001               | 1,0 | 5,5  | 200 | 98  | 7/32"   | 8"     |    |    | 10 |
| 05006125001               | 1,2 | 6,5  | 150 | 105 | 1/4"    | 6"     |    |    | 10 |
| 05006126001               | 1,2 | 6,5  | 200 | 105 | 7/32"   | 8"     |    |    | 10 |
| 05006130001               | 1,2 | 8,0  | 175 | 112 | 5/16"   | 7"     |    |    | 5  |
| 05006135001               | 1,6 | 8,0  | 200 | 112 | 5/16"   | 8"     |    |    | 5  |
| 05006140001               | 1,6 | 10,0 | 200 | 112 | 3/8"    | 8"     |    |    | 5  |

<sup>1)</sup> without Lasertip®

### 162 i PH VDE Insulated Screwdriver for Phillips Screws



**Application:** For Phillips screws  
**Blade:** Insulated  
**Tip:** DIN 5260-PH, ISO 8764-PH, Lasertip®  
**Handle:** Kraftform® with anti-roll protection, multi-component  
**Standard:** IEC 60900 : 2004

| Code                      | mm   | mm  | mm  | mm     | mm | mm | mm | mm | mm |
|---------------------------|------|-----|-----|--------|----|----|----|----|----|
| 05006150001 <sup>1)</sup> | PH 0 | 80  | 81  | 3 1/8" |    |    |    |    | 5  |
| 05006152001               | PH 1 | 80  | 98  | 3 1/8" |    |    |    |    | 5  |
| 05006153001               | PH 1 | 150 | 98  | 6"     |    |    |    |    | 5  |
| 05006154001               | PH 2 | 100 | 105 | 4"     |    |    |    |    | 5  |
| 05006159001               | PH 2 | 200 | 105 | 8"     |    |    |    |    | 5  |
| 05006156001               | PH 3 | 150 | 112 | 6"     |    |    |    |    | 5  |
| 05006158001 <sup>1)</sup> | PH 4 | 200 | 112 | 8"     |    |    |    |    | 2  |

<sup>1)</sup> without Lasertip®

### 165 i PZ VDE Insulated Screwdriver for Pozidriv screws



**Application:** Suitable for Pozidriv®-screws  
**Blade:** Insulated  
**Tip:** ISO 8764-PZ, Lasertip®  
**Handle:** Kraftform® with anti-roll protection, multi-component  
**Standard:** IEC 60900 : 2004

| Code                      | mm   | mm  | mm  | mm     | mm | mm | mm | mm | mm |
|---------------------------|------|-----|-----|--------|----|----|----|----|----|
| 05006160001 <sup>1)</sup> | PZ 0 | 80  | 81  | 3 1/8" |    |    |    |    | 5  |
| 05006162001               | PZ 1 | 80  | 98  | 3 1/8" |    |    |    |    | 5  |
| 05006163001               | PZ 1 | 150 | 98  | 6"     |    |    |    |    | 5  |
| 05006164001               | PZ 2 | 100 | 105 | 4"     |    |    |    |    | 5  |
| 05006165001               | PZ 2 | 200 | 105 | 8"     |    |    |    |    | 5  |
| 05006166001               | PZ 3 | 150 | 112 | 6"     |    |    |    |    | 5  |
| 05006168001 <sup>1)</sup> | PZ 4 | 200 | 112 | 8"     |    |    |    |    | 2  |

<sup>1)</sup> without Lasertip®

<sup>2)</sup> Pozidriv = reg. trademark of European Industrial Service Ltd.

### 162 i PH/S VDE Insulated screwdriver for PlusMinus-screws (Phillips/slotted)



**Application:** For PlusMinus screws (Phillips/slotted)  
**Blade:** Insulated  
**Tip:** PlusMinus (Phillips/slotted)  
**Handle:** Kraftform® with anti-roll protection, multi-component  
**Standard:** IEC 60900 : 2004

| Code        | mm  | mm  | mm  | mm     | mm | mm | mm | mm | mm |
|-------------|-----|-----|-----|--------|----|----|----|----|----|
| 05006380001 | # 1 | 80  | 98  | 3 1/8" |    |    |    |    | 5  |
| 05006381001 | # 2 | 100 | 105 | 4"     |    |    |    |    | 5  |

### 165 i PZ/S VDE Insulated screwdriver for PlusMinus-screws (Pozidriv/slotted)



**Application:** For PlusMinus screws (Pozidriv®/slotted)  
**Blade:** Insulated  
**Tip:** PlusMinus (Pozidriv/slotted)  
**Handle:** Kraftform® with anti-roll protection, multi-component  
**Standard:** IEC 60900 : 2004

| Code        | mm  | mm  | mm  | mm     | mm | mm | mm | mm | mm |
|-------------|-----|-----|-----|--------|----|----|----|----|----|
| 05006190001 | # 1 | 80  | 98  | 3 1/8" |    |    |    |    | 5  |
| 05006191001 | # 2 | 100 | 105 | 4"     |    |    |    |    | 5  |

<sup>2)</sup> Pozidriv = reg. trademark of European Industrial Service Ltd.