

CONNETTORE TIPO A (CON MOLLA DI RITEGNO ESTERNA)
CONNECTOR TYPE A (WITH EXTERNAL SPRING)




SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

SEZIONE A-A
(SECTION A-A)

SEZIONE B-B
(SECTION B-B)




LOGO AMP
(AMP TRADE MARK)

ASSE CAVITA'
(CAVITY CENTER LINE)

TIP. CAVITA' PER TERMINALI AMP JPT P/N 929939-...
OPPURE 929937-... E RELATIVI GOMMINI
AMP P/N 828904-1, 828904-2, 828905-1, 282536-1.
TAPPO CAVITA' P/N 828906-2

(TYP. CAV. FOR JPT CONT. P/N 929939-... A/O 929937-... AND REL.
SINGLE WIRE SEAL P/N 828904-1, 828904-2, 828905-1, 282536-1
CAVITY PLUG P/N 828906-2)



ROSSO (RED)	282762-8
GIALLO (YELLOW)	282762-7
MARRONE (BROWN)	282762-6
BLU (BLUE)	282762-5
VERDE (GREEN)	282762-4
NATURALE (CLEAR)	282762-3
GRIGIO (GREY)	282762-2
NERO (BLACK)	282762-1

COLORE (COLOR)	NUMERO (PART N°)
-------------------	---------------------

3	//////	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)
2	NATURALE (CLEAR)	GOMMA SILICONE (SILICONE RUBBER)	GUARNIZIONE (SEALING)
1	//////	PA 6.6 C.VETRO (PA 6.6 G.F.)	BLOCCHETTO (HOUSING)
N° (ITEM)	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED - RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)	DIAM. ISOLANTE (INS. DIA. RANGE) 1.4-3.0 (RED. INS. CABLE)	RANGO FILO (WIRE RANGE) 0.5-2.5 mm ²	SCALA (SCALE) ---
---	---	---	-------------------------

± 0.3
ANGOLI
(ANGLES) ± 2°

DIS. 24 MAY 96
CONT. A. BAJ

DIS. 24 MAY 96
CONT. C. TARTARI

PRIMA EMISSIONE CON
ET00-0217-95


REV. DATA (DATE)

LOC. SIZE NUMERO
(DWG NO)
I A3 C-282762


REV. FOGLIO
(SHEET)
B1 1 D1 2

DISTRIBUZIONE
(PRINT DIST.)


ASSE CAVITA'
(CAVITY CENTER LINE)



ASSE CONNETTORE
(CONNECTOR CENTER LINE)



DETT. LINGUETTA TAB-SCALA 5:1-
(TAB DETAIL)



FORMA ALTERNATIVA PERMESSA CON RAGGIO
(ALLOWED ALTERNATIVE PROFILE WITH RADIUS)

QUOTE APPLICABILI PER SFORMATURA PEZZO
(DRAFT PERMITTED TO FACILITATE REMOVAL OF PART
FROM THE MOULD)

MATERIALE LINGUETTE: LEGA DI RAME
STAGNATA, ES. OTTONE STAGNATO.
(TAB CONTACT MATERIAL: TIN PLATED COPPER ALLOY,
E.G. BRASS TIN PLATED)

MATERIALE BLOCCHETTO: TERMOPLASTICO
CARICATO FIBRA VETRO.
(HOUSING MATERIAL: THERMOPLASTIC, GLASS FIBER
FILLED)

FINITURA / COLORE
(FINISH / COLOUR) MATERIALE
(MATERIAL) NUMERO
(PART NUMBER)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE: SE NON
DIVERSAMENTE SPECIFICATO
(TOLERANCES: UNLESS
OTHERWISE SPECIFIED)

ANGOLI
(ANGLES) ± 0.3
± 2°

DIS.
(DR.) DESCRIZIONE (DESCRIPTION)
2 POS. SPLASH PROOF CONN. ASS'Y
with SECONDARY LOCK

LOC. SIZE NUMERO
(DWG NO) REV. FOGLIO
(SHEET) I A3 C-282762 B1 2 DI
(OF) 2

SEE SHEET 1 OF 2

SEE SHEET 1 OF 2