

# SPECIFICATION OF RH SERIES

## APPLICATIONS

The RH type bead cores are mainly produced for the cable wire assemblers and MATV CATV makers.

\* Internal and external computer data and power cables


## ORDERING CODE

K5B RH 14.2 x 28.5 x 6.35  
(1) (2) (3) (4) (5)

- (1) MATERIAL
- (2) PRODUCT CODE
- (3) A DIM.
- (4) B DIM.
- (5) C DIM.






## SHAPE



## DIMENSIONS & CHARACTERISTICS

UNIT:mm

| NO. | ORDERING CODE | A         | B          | C         |
|-----|---------------|-----------|------------|-----------|
| 1   | RH 2.5x4x0.8  | 2.50±0.15 | 4.00±0.30  | 0.80±0.15 |
| 2   | RH 2.5x7x0.8  | 2.50±0.15 | 7.00±0.30  | 0.80±0.15 |
| 3   | RH 2.5x12x1.3 | 2.50±0.15 | 12.00±0.40 | 1.30±0.15 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.






KING CORE ELECTRONICS INC.  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE   | A         | B          | C         |
|-----|-----------------|-----------|------------|-----------|
| 4   | RH 3x3x1        | 3.00±0.15 | 3.00±0.20  | 1.00±0.15 |
| 5   | RH 3x3x1.2      | 3.00±0.15 | 3.00±0.20  | 1.20±0.15 |
| 6   | RH 3x4x1        | 3.00±0.15 | 4.00±0.30  | 1.00±0.15 |
| 7   | RH 3x6x1        | 3.00±0.15 | 6.00±0.30  | 1.00±0.15 |
| 8   | RH 3.4x11.2x1.1 | 3.40±0.15 | 11.20±0.40 | 1.10±0.15 |
| 9   | RH 3.5x3.5x0.8  | 3.50±0.15 | 3.50±0.20  | 0.80±0.15 |
| 10  | RH 3.5x3.5x1.2  | 3.50±0.15 | 3.50±0.20  | 1.20±0.15 |
| 11  | RH 3.5x3.5x1.7  | 3.50±0.15 | 3.50±0.20  | 1.70±0.15 |
| 12  | RH 3.5x3.5x1.8  | 3.50±0.15 | 3.50±0.20  | 1.80±0.15 |
| 13  | RH 3.5x4x1      | 3.50±0.15 | 4.00±0.30  | 1.00±0.15 |
| 14  | RH 3.5x4x1.2    | 3.50±0.15 | 4.00±0.30  | 1.20±0.15 |
| 15  | RH 3.5x4x1.3    | 3.50±0.15 | 4.00±0.30  | 1.30±0.15 |
| 16  | RH 3.5x4x1.5    | 3.50±0.15 | 4.00±0.30  | 1.50±0.15 |
| 17  | RH 3.5x4.5x0.8  | 3.50±0.15 | 4.50±0.30  | 0.80±0.15 |
| 18  | RH 3.5x4.7x0.8  | 3.50±0.15 | 4.70±0.30  | 0.80±0.15 |
| 19  | RH 3.5x5x0.8    | 3.50±0.15 | 5.00±0.30  | 0.80±0.15 |
| 20  | RH 3.5x5x1.2    | 3.50±0.15 | 5.00±0.30  | 1.20±0.15 |
| 21  | RH 3.5x5x1.3    | 3.50±0.15 | 5.00±0.30  | 1.30±0.15 |
| 22  | RH 3.5x5x1.5    | 3.50±0.15 | 5.00±0.30  | 1.50±0.15 |
| 23  | RH 3.5x5x1.8    | 3.50±0.15 | 5.00±0.30  | 1.80±0.15 |
| 24  | RH 3.5x6x0.8    | 3.50±0.15 | 6.00±0.30  | 0.80±0.15 |
| 25  | RH 3.5x6x1      | 3.50±0.15 | 6.00±0.30  | 1.00±0.15 |
| 26  | RH 3.5x6x1.2    | 3.50±0.15 | 6.00±0.30  | 1.20±0.15 |
| 27  | RH 3.5x6x1.3    | 3.50±0.15 | 6.00±0.30  | 1.30±0.15 |
| 28  | RH 3.5x6x1.5    | 3.50±0.15 | 6.00±0.30  | 1.50±0.15 |
| 29  | RH 3.5x6x1.8    | 3.50±0.15 | 6.00±0.30  | 1.80±0.15 |
| 30  | RH 3.5x7x1.2    | 3.50±0.15 | 7.00±0.30  | 1.20±0.15 |
| 31  | RH 3.5x7.5x0.8  | 3.50±0.15 | 7.50±0.30  | 0.80±0.15 |
| 32  | RH 3.5x8x0.8    | 3.50±0.15 | 8.00±0.30  | 0.80±0.15 |
| 33  | RH 3.5x8x1      | 3.50±0.15 | 8.00±0.30  | 1.00±0.15 |
| 34  | RH 3.5x9x0.8    | 3.50±0.15 | 9.00±0.30  | 0.80±0.15 |
| 35  | RH 3.5x9x1.3    | 3.50±0.15 | 9.00±0.30  | 1.30±0.15 |
| 36  | RH 3.5x9.5x0.8  | 3.50±0.15 | 9.50±0.30  | 0.80±0.15 |
| 37  | RH 3.5x14x0.8   | 3.50±0.15 | 14.00±0.40 | 0.80±0.15 |



※Other sizes are available upon request.


※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel:886-3-4698855


Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel:886-3-4698855














Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395












No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE     | A         | B          | C         |
|-----|-------------------|-----------|------------|-----------|
| 38  | RH 4x4x1.5        | 4.00±0.20 | 4.00±0.30  | 1.50±0.15 |
| 39  | RH 4x4x2          | 4.00±0.20 | 4.00±0.30  | 2.00±0.15 |
| 40  | RH 4x5x1.5        | 4.00±0.20 | 5.00±0.30  | 1.50±0.15 |
| 41  | RH 4x5x2          | 4.00±0.20 | 5.00±0.30  | 2.00±0.15 |
| 42  | RH 4x5.5x1.5      | 4.00±0.20 | 5.50±0.30  | 1.50±0.15 |
| 43  | RH 4x6x2          | 4.00±0.20 | 6.00±0.30  | 2.00±0.15 |
| 44  | RH 4x7x2          | 4.00±0.20 | 7.00±0.30  | 2.00±0.15 |
| 45  | RH 4x8x2          | 4.00±0.20 | 8.00±0.30  | 2.00±0.15 |
| 46  | RH 4x10x1.5       | 4.00±0.20 | 10.00±0.40 | 1.50±0.15 |
| 47  | RH 4x10x2         | 4.00±0.20 | 10.00±0.40 | 2.00±0.15 |
| 48  | RH 4x12x2         | 4.00±0.20 | 12.00±0.40 | 2.00±0.15 |
| 49  | RH 4x12.5x1.5     | 4.00±0.20 | 12.50±0.40 | 1.50±0.15 |
| 50  | RH 4x15x2         | 4.00±0.20 | 15.00±0.40 | 2.00±0.15 |
| 51  | RH 4x17x2         | 4.00±0.20 | 17.00±0.40 | 2.00±0.15 |
| 52  | RH 4.5x4.8x2.5    | 4.50±0.20 | 4.80±0.30  | 2.50±0.15 |
| 53  | RH 4.5x7x2.5      | 4.50±0.20 | 7.00±0.30  | 2.50±0.15 |
| 54  | RH 4.5x12x2.6     | 4.50±0.20 | 12.00±0.40 | 2.60±0.15 |
| 55  | RH 4.6x11x2       | 4.60±0.20 | 11.00±0.40 | 2.00±0.15 |
| 56  | RH 4.83x6.35x2.29 | 4.83±0.20 | 6.35±0.30  | 2.29±0.15 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel: 886-3-4698855


Fax: 886-3-4691395

E-mail: kc@mail.kingcore.com.tw

No.269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel:886-3-4698855

Fax:886-3-4691395
















No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE  | A         | B          | C         |
|-----|----------------|-----------|------------|-----------|
| 57  | RH 5x5x2.3     | 5.00±0.20 | 5.00±0.30  | 2.30±0.15 |
| 58  | RH 5x6.2x1.6   | 5.00±0.20 | 6.20±0.30  | 1.60±0.15 |
| 59  | RH 5x6.35x1.5  | 5.00±0.20 | 6.35±0.30  | 1.50±0.15 |
| 60  | RH 5x6.35x2.36 | 5.00±0.20 | 6.35±0.30  | 2.36±0.15 |
| 61  | RH 5x10x2.3    | 5.00±0.20 | 10.00±0.40 | 2.30±0.15 |
| 62  | RH 5x11x1.5    | 5.00±0.20 | 11.00±0.40 | 1.50±0.15 |
| 63  | RH 5x12x2.15   | 5.00±0.20 | 12.00±0.40 | 2.15±0.15 |
| 64  | RH 5x18x2.15   | 5.00±0.20 | 18.00±0.40 | 2.15±0.15 |
| 65  | RH 5x20x1.5    | 5.00±0.20 | 20.00±0.50 | 1.50±0.15 |
| 66  | RH 5.7x8x1.5   | 5.70±0.20 | 8.00±0.30  | 1.50±0.15 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only. King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395
















No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE    | A         | B          | C         |
|-----|------------------|-----------|------------|-----------|
| 67  | RH 6x10x3        | 6.00±0.20 | 10.00±0.40 | 3.00±0.20 |
| 68  | RH 6x10x4        | 6.00±0.20 | 10.00±0.40 | 4.00±0.20 |
| 69  | RH 6x12.8x4      | 6.00±0.20 | 12.80±0.40 | 4.00±0.20 |
| 70  | RH 6x18x3.15     | 6.00±0.20 | 18.00±0.40 | 3.15±0.20 |
| 71  | RH 6x25x3        | 6.00±0.20 | 25.00±0.60 | 3.00±0.20 |
| 72  | RH 6.35x12.7x3.3 | 6.35±0.20 | 12.70±0.40 | 3.30±0.20 |
| 73  | RH 6.35x15.8x3.3 | 6.35±0.20 | 15.80±0.40 | 3.30±0.20 |
| 74  | RH 6.5x10x4.3    | 6.50±0.20 | 10.00±0.40 | 4.30±0.20 |
| 75  | RH 6.5x11x4.3    | 6.50±0.20 | 11.00±0.40 | 4.30±0.20 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395








No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE  | A         | B          | C         |
|-----|----------------|-----------|------------|-----------|
| 76  | RH 7.5x7.5x2.4 | 7.50±0.20 | 7.50±0.30  | 2.40±0.15 |
| 77  | RH 7.9x10x3    | 7.90±0.20 | 10.00±0.40 | 3.00±0.20 |
| 78  | RH 7.9x12.8x4  | 7.90±0.20 | 12.80±0.40 | 4.00±0.20 |
| 79  | RH 7.9x19x3    | 7.90±0.20 | 19.00±0.40 | 3.00±0.20 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.










**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE   | A         | B          | C         |
|-----|-----------------|-----------|------------|-----------|
| 80  | RH 8x9x6        | 8.00±0.20 | 9.00±0.30  | 6.00±0.30 |
| 81  | RH 8x9.8x6      | 8.00±0.20 | 9.80±0.30  | 6.00±0.30 |
| 82  | RH 8x10x4       | 8.00±0.20 | 10.00±0.40 | 4.00±0.20 |
| 83  | RH 8x10.06x3.18 | 8.00±0.20 | 10.06±0.40 | 3.18±0.20 |
| 84  | RH 8x12x6       | 8.00±0.20 | 12.00±0.40 | 6.00±0.30 |
| 85  | RH 8x16x5       | 8.00±0.20 | 16.00±0.40 | 5.00±0.25 |
| 86  | RH 8x20x5       | 8.00±0.20 | 20.00±0.50 | 5.00±0.25 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.









**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES


| NO. | ORDERING CODE      | A         | B          | C         |
|-----|--------------------|-----------|------------|-----------|
| 87  | RH 9x10x4.5        | 9.00±0.30 | 10.00±0.40 | 4.50±0.20 |
| 88  | RH 9x16x5          | 9.00±0.30 | 16.00±0.40 | 5.00±0.25 |
| 89  | RH 9.3x9.5x4.5     | 9.30±0.30 | 9.50±0.30  | 4.50±0.20 |
| 90  | RH 9.3x11x5.8      | 9.30±0.30 | 11.00±0.40 | 5.80±0.25 |
| 91  | RH 9.5x9.5x4.8     | 9.50±0.30 | 9.50±0.30  | 4.80±0.20 |
| 92  | RH 9.5x9.5x5.2     | 9.50±0.30 | 9.50±0.30  | 5.20±0.25 |
| 93  | RH 9.5x10x5.2      | 9.50±0.30 | 10.00±0.40 | 5.20±0.25 |
| 94  | RH 9.5x10x5.8      | 9.50±0.30 | 10.00±0.40 | 5.80±0.25 |
| 95  | RH 9.5x10.4x5      | 9.50±0.30 | 10.40±0.40 | 5.00±0.25 |
| 96  | RH 9.5x12.7x4.8    | 9.50±0.30 | 12.70±0.40 | 4.80±0.20 |
| 97  | RH 9.5x14.5x5      | 9.50±0.30 | 14.50±0.40 | 5.00±0.25 |
| 98  | RH 9.5x15.88x5     | 9.50±0.30 | 15.88±0.40 | 5.00±0.25 |
| 99  | RH 9.5x16x5        | 9.50±0.30 | 16.00±0.40 | 5.00±0.25 |
| 100 | RH 9.5x19x5        | 9.50±0.30 | 19.00±0.40 | 5.00±0.25 |
| 101 | RH 9.5x19.5x5      | 9.50±0.30 | 19.50±0.40 | 5.00±0.25 |
| 102 | RH 9.52x15.88x5.08 | 9.52±0.30 | 15.88±0.40 | 5.08±0.25 |
| 103 | RH 9.8x11.4x0.8    | 9.80±0.30 | 11.40±0.40 | 0.80±0.15 |
| 104 | RH 9.8x13.5x6.7    | 9.80±0.30 | 13.50±0.40 | 6.70±0.30 |
| 105 | RH 9.8x19.05x6.7   | 9.80±0.30 | 19.05±0.40 | 6.70±0.30 |
| 106 | RH 9.8x25x3.8      | 9.80±0.30 | 25.00±0.60 | 3.80±0.30 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

# SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel: 886-3-4698855

Fax: 886-3-4691395









No. 269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

E-mail: [kc@mail.kingcore.com.tw](mailto:kc@mail.kingcore.com.tw)

Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE  | A          | B          | C         |
|-----|----------------|------------|------------|-----------|
| 107 | RH 10x10x5     | 10.00±0.30 | 10.00±0.40 | 5.00±0.25 |
| 108 | RH 10x10x6     | 10.00±0.30 | 10.00±0.40 | 6.00±0.30 |
| 109 | RH 10x10x7     | 10.00±0.30 | 10.00±0.40 | 7.00±0.30 |
| 110 | RH 10x14x6     | 10.00±0.30 | 14.00±0.40 | 6.00±0.30 |
| 111 | RH 10.5x20x5.5 | 10.50±0.30 | 20.00±0.50 | 5.50±0.25 |
| 112 | RH 10.5x25x5.5 | 10.50±0.30 | 25.00±0.60 | 5.50±0.25 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.











KING CORE ELECTRONICS INC.  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE  | A          | B          | C         |
|-----|----------------|------------|------------|-----------|
| 113 | RH 11x16x5     | 11.00±0.30 | 16.00±0.40 | 5.00±0.25 |
| 114 | RH 11x18.5x5   | 11.00±0.30 | 18.50±0.40 | 5.00±0.25 |
| 115 | RH 11x20x5     | 11.00±0.30 | 20.00±0.50 | 5.00±0.25 |
| 116 | RH 11x25x5     | 11.00±0.30 | 25.00±0.60 | 5.00±0.25 |
| 117 | RH 11.5x18.5x5 | 11.50±0.30 | 18.50±0.40 | 5.00±0.25 |
| 118 | RH 11.5x20x4.3 | 11.50±0.30 | 20.00±0.50 | 4.30±0.20 |
| 119 | RH 11.5x26x4.3 | 11.50±0.30 | 26.00±0.60 | 4.30±0.20 |
| 120 | RH 11.8x15x7.3 | 11.80±0.30 | 15.00±0.40 | 7.30±0.30 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.















KING CORE ELECTRONICS INC.  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE      | A          | B          | C         |
|-----|--------------------|------------|------------|-----------|
| 121 | RH 12x12x7         | 12.00±0.30 | 12.00±0.40 | 7.00±0.30 |
| 122 | RH 12x12x8.5       | 12.00±0.30 | 12.00±0.40 | 8.50±0.30 |
| 123 | RH 12x15x5.6       | 12.00±0.30 | 15.00±0.40 | 5.60±0.25 |
| 124 | RH 12x15x7         | 12.00±0.30 | 15.00±0.40 | 7.00±0.30 |
| 125 | RH 12x15x8.5       | 12.00±0.30 | 15.00±0.40 | 8.50±0.30 |
| 126 | RH 12x20x5.6       | 12.00±0.30 | 20.00±0.50 | 5.60±0.25 |
| 127 | RH 12x20x7.3       | 12.00±0.30 | 20.00±0.50 | 7.30±0.30 |
| 128 | RH 12x30x5.6       | 12.00±0.30 | 30.00±0.70 | 5.60±0.25 |
| 129 | RH 12.2x23x7.9     | 12.20±0.30 | 23.00±0.50 | 7.90±0.30 |
| 130 | RH 12.3x20x7       | 12.30±0.30 | 20.00±0.50 | 7.00±0.30 |
| 131 | RH 12.32x25.4x4.88 | 12.32±0.30 | 25.40±0.60 | 4.88±0.20 |
| 132 | RH 12.5x12.5x8     | 12.50±0.30 | 12.50±0.40 | 8.00±0.30 |
| 133 | RH 12.5x15x5.2     | 12.50±0.30 | 15.00±0.40 | 5.20±0.25 |
| 134 | RH 12.7x12.7x7.9   | 12.70±0.30 | 12.70±0.40 | 7.90±0.30 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855









Fax:886-3-4691395

E-mail:kc@mail.kingcore.com.tw

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.















**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES




| NO. | ORDERING CODE       | A          | B          | C         |
|-----|---------------------|------------|------------|-----------|
| 135 | RH 14x15x9          | 14.00±0.40 | 15.00±0.40 | 9.00±0.30 |
| 136 | RH 14.2x15x6.35     | 14.20±0.40 | 15.00±0.40 | 6.35±0.30 |
| 137 | RH 14.2x15x7        | 14.20±0.40 | 15.00±0.40 | 7.00±0.30 |
| 138 | RH 14.2x15x8        | 14.20±0.40 | 15.00±0.40 | 8.00±0.30 |
| 139 | RH 14.2x18x6.35     | 14.20±0.40 | 18.00±0.40 | 6.35±0.30 |
| 140 | RH 14.2x23.5x7      | 14.20±0.40 | 23.50±0.50 | 7.00±0.30 |
| 141 | RH 14.2x28.5x6.35   | 14.20±0.40 | 28.50±0.60 | 6.35±0.30 |
| 142 | RH 14.2x28.5x7      | 14.20±0.40 | 28.50±0.60 | 7.00±0.30 |
| 143 | RH 14.2x28.5x8      | 14.20±0.40 | 28.50±0.60 | 8.00±0.30 |
| 144 | RH 14.99x19x6.99    | 14.99±0.40 | 19.00±0.40 | 6.99±0.30 |
| 145 | RH 14.99x27.94x6.99 | 14.99±0.40 | 27.94±0.60 | 6.99±0.30 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

# SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel:886-3-4698855

Fax:886-3-4691395









No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE       | A          | B          | C          |
|-----|---------------------|------------|------------|------------|
| 146 | RH 15.2x28.5x10.2   | 15.20±0.40 | 28.50±0.60 | 10.20±0.40 |
| 147 | RH 15.25x17x9       | 15.25±0.40 | 17.00±0.40 | 9.00±0.30  |
| 148 | RH 15.25x28x8       | 15.25±0.40 | 28.00±0.60 | 8.00±0.30  |
| 149 | RH 15.65x28.57x6.99 | 15.65±0.40 | 28.57±0.60 | 6.99±0.30  |
| 150 | RH 15.8x16x7.9      | 15.80±0.40 | 16.00±0.40 | 7.90±0.30  |
| 151 | RH 15.88x28.57x7.87 | 15.88±0.40 | 28.57±0.60 | 7.87±0.30  |

















※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE  | A          | B          | C          |
|-----|----------------|------------|------------|------------|
| 152 | RH 16x16x8     | 16.00±0.40 | 16.00±0.40 | 8.00±0.30  |
| 153 | RH 16x17x9     | 16.00±0.40 | 17.00±0.40 | 9.00±0.30  |
| 154 | RH 16x17.5x4.3 | 16.00±0.40 | 17.50±0.40 | 4.30±0.20  |
| 155 | RH 16x20x7     | 16.00±0.40 | 20.00±0.50 | 7.00±0.30  |
| 156 | RH 16x20x9     | 16.00±0.40 | 20.00±0.50 | 9.00±0.30  |
| 157 | RH 16x28x7     | 16.00±0.40 | 28.00±0.60 | 7.00±0.30  |
| 158 | RH 16x28x9     | 16.00±0.40 | 28.00±0.60 | 9.00±0.30  |
| 159 | RH 16x28x10    | 16.00±0.40 | 28.00±0.60 | 10.00±0.40 |
| 160 | RH 16x28.5x9   | 16.00±0.40 | 28.50±0.60 | 9.00±0.30  |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395













No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE      | A          | B          | C          |
|-----|--------------------|------------|------------|------------|
| 161 | RH 17.07x25.4x8.76 | 17.07±0.40 | 25.40±0.60 | 8.76±0.30  |
| 162 | RH 17.5x23.5x9.5   | 17.50±0.40 | 23.50±0.50 | 9.50±0.30  |
| 163 | RH 17.5x28.5x8     | 17.50±0.40 | 28.50±0.60 | 8.00±0.30  |
| 164 | RH 17.5x28.5x8.3   | 17.50±0.40 | 28.50±0.60 | 8.30±0.30  |
| 165 | RH 17.5x28.5x9.5   | 17.50±0.40 | 28.50±0.60 | 9.50±0.30  |
| 166 | RH 17.5x28.5x10.7  | 17.50±0.40 | 28.50±0.60 | 10.70±0.40 |
| 167 | RH 17.5x35x9.5     | 17.50±0.40 | 35.00±0.80 | 9.50±0.30  |










※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE        | A          | B          | C          |
|-----|----------------------|------------|------------|------------|
| 168 | RH 18x18x10          | 18.00±0.50 | 18.00±0.40 | 10.00±0.40 |
| 169 | RH 18x28x10          | 18.00±0.50 | 28.00±0.60 | 10.00±0.40 |
| 170 | RH 18x29x10          | 18.00±0.50 | 29.00±0.60 | 10.00±0.40 |
| 171 | RH 18.67x25x10.16    | 18.67±0.50 | 25.00±0.60 | 10.16±0.40 |
| 172 | RH 18.67x28.57x10.16 | 18.67±0.50 | 28.57±0.60 | 10.16±0.40 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395





No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE  | A          | B          | C          |
|-----|----------------|------------|------------|------------|
| 173 | RH 19x29x13    | 19.00±0.50 | 29.00±0.60 | 13.00±0.40 |
| 174 | RH 19x31.5x5.8 | 19.00±0.50 | 31.50±0.70 | 5.80±0.25  |
| 175 | RH 19x35x5.8   | 19.00±0.50 | 35.00±0.80 | 5.80±0.25  |
| 176 | RH 19x35x6.3   | 19.00±0.50 | 35.00±0.80 | 6.30±0.30  |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel: 886-3-4698855

Fax: 886-3-4691395


E-mail: [kc@mail.kingcore.com.tw](mailto:kc@mail.kingcore.com.tw)

No. 269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE    | A          | B          | C          |
|-----|------------------|------------|------------|------------|
| 177 | RH 20x28.25x14.5 | 20.00±0.60 | 28.25±0.60 | 14.50±0.50 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel: 886-3-4698855

Fax: 886-3-4691395



No. 269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

E-mail: [kc@mail.kingcore.com.tw](mailto:kc@mail.kingcore.com.tw)

Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE        | A          | B          | C          |
|-----|----------------------|------------|------------|------------|
| 178 | RH 25.91x28.57x12.83 | 25.91±0.60 | 28.57±0.60 | 12.83±0.40 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel:886-3-4698855

Fax:886-3-4691395




No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF RH SERIES

| NO. | ORDERING CODE       | A          | B          | C          |
|-----|---------------------|------------|------------|------------|
| 179 | RH 28x28x16         | 28.00±0.60 | 28.00±0.60 | 16.00±0.50 |
| 180 | RH 28.5x28.57x13.77 | 28.50±0.60 | 28.57±0.60 | 13.77±0.40 |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw