



LOC	DIST	P	F	REVISIONS						
				ZONE	LTR	DESCRIPTION			DATE	APPD
G	86				S	REV & REDRA PER G-5357			02/28/90	PKS



1 CIRCULAR MIL AREA RANGE: 33,100-52,600 CM
2 TIN PL 0.00381 [0.000150] MIN THK PER MIL-T-10727



				PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-152		DR 02/28/90 DK SCHRUM		AMP AMP INCORPORATED Harrisburg, Pa. 17105		
		CHK 19JAN95 MS FEHER				
		APPD 19JAN95 WJ VOCKROTH				
FINISH △ 2		APPD 19JAN95 TL SHUTTER		NAME TERMINAL, AMPPOWER™, WIRE SIZE: 4 AWG		
		PRODUCT SPEC 108-30200				
		APPLICATION SPEC -		SIZE C	CAGE CODE 00779	DRAWING NO 328162
		WEIGHT .017 LB		SCALE 4:1		SHEET 1 OF 1

